

### BIZ1 - Bizweld Work FR Coverall

**Collection:** Bizweld™ Work

**Range:** Flame Resistant Multi-Norm

**Shell Fabric:** Bizweld Work: 100% Cotton, 330g

**Outer Carton:** 12

#### Product information

Voted the number one favourite coverall in the welding industry, our best selling Bizweld coverall is ideal for offering complete protection to workers exposed to heat. The generous fit provides comfort and allows the wearer to work unhindered whilst ample storage space, rule pocket and concealed mobile phone pocket hold equipment securely and safely.

#### Bizweld™ Work

Bizweld™ Work protective clothing have been specially designed to guarantee comfort, performance and safety whilst providing effective function at all times. Bizweld™ Work has been rigorously tested to ensure total compliance with the latest international standards.

#### Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

#### Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 1 (A1+A2)

IEC 61482-2 IEC 61482-1-1 (ELIM 8.3 CAL/CM<sup>2</sup>, ATPV 10.9 CAL/CM<sup>2</sup>)

ASTM F1959/F1959M-12 (ATPV 11.2 CAL/CM<sup>2</sup> (HAF = 80.4%))



#### Features

- Protection against radiant, convective and contact heat
- Certified protection against molten metal splash
- Concealed stud front for easy access
- Chest pockets with stud closure
- Stud adjustable cuffs for a secure fit
- Rule pocket
- Radio loop for easy clipping of a radio
- Concealed phone pocket
- 6 pockets for ample storage
- CE-CAT III
- CE certified

## BIZ1 - Bizweld Work FR Coverall

**Commodity Code: 6211321000**

### Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

Cert No: 2777/12872-03/E00-00

### Wash Care



### Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m <sup>3</sup> )	EAN13	GTIN/DUN14
BIZ1GRRS	Grey	43.0	28.0	52.0	1.2200	0.0626	5036108190003	15036108676740
BIZ1GRRM	Grey	43.0	28.0	52.0	0.3200	0.0626	5036108190010	15036108676733
BIZ1GRRL	Grey	43.0	28.0	58.0	1.2900	0.0698	5036108190027	15036108676726
BIZ1GRRXL	Grey	43.0	28.0	58.0	1.3900	0.0698	5036108190034	15036108676757
BIZ1GRRXXL	Grey	43.0	28.0	58.0	1.4200	0.0698	5036108190041	15036108676771
BIZ1GRRXXXL	Grey	43.0	28.0	58.0	1.4500	0.0698	5036108190058	15036108676788