

Product datasheet

Specifications



Set of cable gland + nut stainless steel M20 AISI304L, IP68, UL approved

NSYCGX20

EAN Code: 3606481360236

Main

Range	PanelSeT
Product or component type	Cable gland
Accessory / separate part category	Cable management accessory
Range compatibility	PanelSeT PanelSeT CRN PanelSeT PanelSeT S3D PanelSeT PanelSeT S3X
Mounting location	Enclosure top Enclosure bottom
Cable entry	Cable gland M20
Device composition	1 cable gland 1 lock nut 1 seal
Quantity per set	Set of 4
Material	Seal: CR (chloroprene) Body: stainless steel AISI 304L

Complementary

Colour	Grey
Fixing mode	Screwed By nut
Height	36 mm
Net weight	0.034 kg

Environment

Product certifications	VDE
Flame retardance	V2 conforming to UL 94
Ambient air temperature for operation	-20...100 °C permanent -40...150 °C intermittent
IP degree of protection	IP68 conforming to IEC 60529 5 bar, 30 min

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	3.000 cm
Package 1 Length	3.500 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	39.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	40
Package 2 Height	11.000 cm
Package 2 Width	28.500 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.938 kg
Unit Type of Package 3	P12
Number of Units in Package 3	960
Package 3 Height	47.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	67.500 kg

Logistical informations

Country of origin	TR
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)

Use Again

 Repack and remanufacture	
Take-back	No