

# RC-Z2430 - Cable clamp type cage and shield adapter



1604503

<https://www.phoenixcontact.com/gb/products/1604503>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable clamp type cage and shield adapter, shielded: yes, litz wire bundle diameter: 4.1 mm, cable diameter range: 4.5 mm ... 5.5 mm, series: NC, RC, this item is undergoing a smooth changeover, lead-free alternative in accordance with RoHS II without exception 6c (Pb < 0.1%) possible on request in advance

## Commercial data

Item number	1604503
Packing unit	1 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	ABRAFU
Product key	ABRAFU
GTIN	4046356249621
Weight per piece (including packing)	9.8 g
Weight per piece (excluding packing)	5.404 g
Customs tariff number	39269097
Country of origin	DE

# RC-Z2430 - Cable clamp type cage and shield adapter



1604503

<https://www.phoenixcontact.com/gb/products/1604503>

## Technical data

### Product properties

Product type	Cable clamp type cage
Series	NC
	RC
Type of the screw connection	EMC
Shielded	yes

### Cable/line

External cable diameter	4.5 mm ... 5.5 mm
-------------------------	-------------------

### Mechanical properties

#### Mechanical data

Type of the screw connection	EMC
------------------------------	-----

# RC-Z2430 - Cable clamp type cage and shield adapter



1604503

<https://www.phoenixcontact.com/gb/products/1604503>

## Classifications

### ECLASS

ECLASS-13.0	27140801
-------------	----------

### ETIM

ETIM 9.0	EC000441
----------	----------

### UNSPSC

UNSPSC 21.0	39121300
-------------	----------

# RC-Z2430 - Cable clamp type cage and shield adapter



1604503

<https://www.phoenixcontact.com/gb/products/1604503>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	e73577b5-4172-40a4-876f-ebc478dcd715

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)