



Socket

52

Product no. **03030021**
GTIN **4018754005932**
Model **52 21**



Label. 1/2 " Socket Spanner size 21mm L.42mm

Properties.

- hex with AS-Drive profile
- 1/2" internal square drive
- HPQ® high performance steel, chrome-plated
- DIN 3124 / ISO 2725-1 / ASME B 107.5M / DIN EN 3709


Technologies and features.



High Performance Quality (HPQ®)

Our HPQ® tool is made of wear-resistant high-performance steel, yet is thin-walled and lightweight. It withstands high torques and is ideal for work in confined spaces such as turbines.

Technical drawing.



Technical attributes.

Drive profile	hex AS-Drive
Internal square drive (inch)	1/2 "
d1	28,7 mm
d2	26 mm
d3	20 mm
DIN	DIN 3124 / ISO 2725-1, ASME B 107.5M, DIN EN 3709
Length mm (L)	42 mm
Width across flats [mm]	21 mm
t1	16 mm
t2	25,2 mm

Logistics data.

Depth mm (IFS)	42
Width mm (IFS)	29
Height mm (IFS)	29
WEEE/ElektroG	nicht ear-pflichtig
Length (packed, mm)	158
Width (packed, mm)	63
Height (packed, mm)	44
Volume (packed, dm3)	0.437976 dm3
Art. no.	03030021
Weight (gross, kg)	1,108
Weight PAP (kg)	0,000
Weight PVC (kg)	0,007
GTIN	4018754005932
Country of origin AWR	GERMANY
Region of origin	Nordrhein-Westfalen
Customs tariff no.	82042000
Packing standard	10
Weight	110 g

Variants.

Art. no.	Model no. (ERP)	Description	GTIN
03030008	52 8	1/2 " Socket Spanner size 8mm L.38mm	4018754005802
03030009	52 9	1/2 " Socket Spanner size 9mm L.38mm	4018754005819
03030010	52 10	1/2 " Socket Spanner size 10mm L.38mm	4018754005826
03030011	52 11	1/2 " Socket Spanner size 11mm L.38mm	4018754005833
03030012	52 12	1/2 " Socket Spanner size 12mm L.38mm	4018754005840
03030013	52 13	1/2 " Socket Spanner size 13mm L.38mm	4018754005857
03030014	52 14	1/2 " Socket Spanner size 14mm L.38mm	4018754005864
03030015	52 15	1/2 " Socket Spanner size 15mm L.38mm	4018754005871
03030016	52 16	1/2 " Socket Spanner size 16mm L.38mm	4018754005888
03030017	52 17	1/2 " Socket Spanner size 17mm L.38mm	4018754005895
03030018	52 18	1/2 " Socket Spanner size 18mm L.38mm	4018754005901
03030019	52 19	1/2 " Socket Spanner size 19mm L.38mm	4018754005918
03030020	52 20	1/2 " Socket Spanner size 20mm L.42mm	4018754005925
03030021	52 21	1/2 " Socket Spanner size 21mm L.42mm	4018754005932

03030022	52 22	1/2 " Socket Spanner size 22mm L.42mm	4018754005949
03030023	52 23	1/2 " Socket Spanner size 23mm L.42mm	4018754005956
03030024	52 24	1/2 " Socket Spanner size 24mm L.42mm	4018754005963
03030025	52 25	1/2 " Socket Spanner size 25mm L.42mm	4018754005970
03030026	52 26	1/2 " Socket Spanner size 26mm L.42mm	4018754005987
03030027	52 27	1/2 " Socket Spanner size 27mm L.45mm	4018754005994
03030028	52 28	1/2 " Socket Spanner size 28mm L.45mm	4018754006007
03030030	52 30	1/2 " Socket Spanner size 30mm L.45mm	4018754006021
03030032	52 32	1/2 " Socket Spanner size 32mm L.47mm	4018754006038
03030034	52 34	1/2 " Socket Spanner size 34mm L.47mm	4018754006045
03030036	52 36	1/2 " Socket Spanner size 36mm L.52mm	4018754283675

GTIN.



STAHLWILLE Eduard Wille GmbH & Co. KG

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0 · Fax: +49 202 4791-393

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH & Co. KG, Wuppertal