

3380879

WWR2900

PEN BARCODE SCANNER



Big Business Tools. Small Business Attitude.

Whether you need quick access to data from an invoice, membership card, or any bar coded material, the Wasp WWR2900 & WWR2905 are the perfect tools for repetitive data entry. These Pen-Style scanners are the reliable, cost-effective way to read bar codes. Scanned data appears on your screen as if you typed it from your keyboard. Scan into any DOS or Windows application, it takes just minutes to set up. Increase your productivity and reduce costly data entry errors with the easy to use WWR2900 and WWR2905 Pen scanners.

WASP WWR2900 FEATURES

- ▶ Ergonomic design
- ▶ Light weight
- ▶ Economical
- ▶ Compact
- ▶ Durable
- ▶ Superior optics
- ▶ Quick connect

BENEFITS

- ▶ Pen style design with soft grip for comfort
- ▶ Less fatigue for repetitive jobs
- ▶ Cost friendly
- ▶ Desktop design, requires minimal space
- ▶ Manufactured from high quality ABS plastic
- ▶ Aggressive first time scan rates
- ▶ Easily connect via PS2 with the WWR 2900 or USB with the WWR 2905

WASP WWR2900 COMMON USES

- | | |
|-------------|---------------|
| ▶ Office | ▶ Government |
| ▶ Libraries | ▶ Retail |
| ▶ Medical | ▶ Field Sales |
| ▶ Marketing | ▶ Tool Room |

3380879

WWR2900

PEN BARCODE SCANNER



Big Business Tools. Small Business Attitude.

■ SPECIFICATIONS

OPTICAL FEATURES	Depth of field: 1mm Resolution: 0.127mm (5 mil) Rate: 100mm - 600mm / Sec Tilt angle: 45 - 90 degree
ELECTRICAL CHARACTERISTICS	Light source: 650nm LED Sensor: Photo Diode Supply voltage: 5 VDC ± 10% Surge power: < 500mA Working current (WWR2900): 45mA ± 10mA Working current (WWR2905): 60mA ± 10mA
MECHANICAL CHARACTERISTICS	Dimensions: 150mm W x 29.6mm H x 22mm D Net weight: 76g Cable: 6 foot coil
ENVIRONMENT CHARACTERISTICS	Operating temperature: 0°C - 50°C Storage temperature: -20°C to 60°C Relative humidity: 0% RH to 95% RH non-condensing Mechanical shock: 6.06ft (1.85) Drop onto concrete Safety certification: FCC class A and CE approval
1D (LINEAR) SYMBOLOGIES READ	Codabar, Code 3 of 9 (Code 39), Code 3 of 9 Full ASCII, Code 11, Code 32, Code 93, Code 128 (including UCC/EAN 128), EAN/JAN-8 (plus supplements), EAN/JAN-13 (plus supplements), Industrial 2 of 5 (25), Interleaved 2 of 5, ISBN, Matrix 25, MSI Plessey, UPC-A (plus supplements), UPC-E (plus supplements), China Post Code, RSS14, Telepen
PART NUMBERS	WWR2905 Pen Barcode Scanner with USB cable: 633808502782 WWR2900 Pen Barcode Scanner with PS2 cable: 633808501044 WWR2900 Pen Barcode Scanner Stand: 633808502799