

Socket set 1/4" on clip rail, 10-pcs.

40aD/10-12916



Product no. **96015310**
GTIN **4018754125272**
Model **40aD/10-12916**



Label.

1/4 " Socket set on clip rail 40aD/10-12916 10 pcs.

Properties.

- bi-hex with AS-Drive profile
- secure fixing to plastic clips with ball locking function
- can be mounted on a wall or perforated wall/panel
- HPQ® high performance steel, chrome-plated
- ASME B 107.1 / Fed. Spec. GGG-W-641 / SAE AS 954-E

Contains 10-pieces:

10 sockets with bi-hex 1/4" No. 40aD: 3/16; 7/32; 1/4; 9/32; 5/16; 11/32; 3/8; 7/16; 1/2; 9/16"

+ socket clip rail No. 12916/10



Technologies and features.



High Performance Quality (HPQ®)

Our HPQ® tool is made of wear-resistant high-performance steel, yet is thin-walled and lightweight. It withstands high torques and is ideal for work in confined spaces such as turbines.

Technical attributes.

Square drive inner (inch)	1/4 "
Number of tools	10 pcs.

Logistics data.

Depth mm (IFS)	347
Width mm (IFS)	100
Height mm (IFS)	24
WEEE/ElektroG	nicht ear-pflichtig
Length (packaged, mm)	347
Width (packaged, mm)	100
Height (packaging, mm)	24
Volume (packaged, dm3)	0.8328 dm3
Product no.	96015310
Weight (gross, kg)	0,200
Weight PAP (kg)	0,000
Weight PVC (kg)	0,000
GTIN	4018754125272
Country of origin AWR	GERMANY
Region of origin	Nordrhein-Westfalen
Customs tariff no.	82042000
Packing standard	1
Weight (g)	200 g

Parts list.



80400003
Socket clip rail



01530034
Sockets



01530032
Sockets



01530028
Sockets



01530024
Sockets



01530022
Sockets



01530020
Sockets



01530018
Sockets



01530016
Sockets



01530014
Sockets



01530012
Sockets



01530012
Sockets

Variants.

Product no.	Model No. (ERP)	Description	GTIN
96015310	40aD/10-12916	1/4 " Socket set on clip rail 40aD/ 10-12916 10 pcs.	4018754125272

GTIN.



Images.



STAHLWILLE Eduard Wille GmbH

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH, Wuppertal