


2029462 DSBG-160-25-PPVA-N3 standards-based cylinder - Series: All



2029462 DSBG-160-25-PPVA-N3 standards-based cylinder - Series: All

Pos.	Part no.	Type	Note	Qty.	Unit
A	8025174	DSBG-160- - Set of wearing parts	Spare parts: 3, 6, 7, 9, 13, 15, 16, 22, 23	1	PC
1	1721255	DSBG-160/200 Collar nut	Tightening torque 100 Nm / 73.8 lbf ft Use locking compound. See position 23	8	PC
2	214862	DIN 439-B-M36X2-04 Hex nut		1	PC
3	224143	WIFC6-40X50X11,5-NBR Wiper seal	Grease using during assembly. See position 22	1	PC
4		40X44X20-4020-DP4 Bearing bushing	Not available separately, see position 8	2	PC
5		DSBG-160-PPV Bearing cap	Not available separately, see position 8	1	PC
6		B-152X4-N-NBR75 O-ring ISO3601	Not available separately, see position A Grease using during assembly. See position 22	2	PC
7		50,0X67,0X10,0 Buffer seal	Not available separately, see position 8+21+999 Grease using during assembly. See position 22	1	PC
8	8193956	DSBG-160-PPV Bearing cap module		1	PC
9		DSBG-160/200-NBR80 Cushioning	Not available separately, see position A	2	PC
10	8025389	DSBG-YZ-160- - Tie rod	When ordering please specify the stroke (see type plate)	4	PC
11	8025352	DSBG-YP-160- - Piston rod	When ordering please specify the configuration (see type plate)	1	PC
12	390679	160/200 PPV Buffer sleeve		2	PC
13		160X145X10:E 4 Lip ring	Not available separately, see position A Grease using during assembly. See position 22	2	PC
14		DSBG-160 Piston	Not available	1	PC
15		DN -160 Guiding band	Not available separately, see position A	1	PC
16		B-20X2-N-NBR70 O-ring ISO3601	Not available separately, see position A Grease using during assembly. See position 22	1	PC
17	216910	7X7X465,0 Magnetic tape		1	PC
18	1670365	DSBG-160/200 Threaded coupling	Tightening torque 330 Nm / 243.4 lbf ft Use locking compound. See position 23	1	PC
19		DSBG-160-... Cylinder barrel	Not available Grease using during assembly. See position 22	1	PC
20		DSBG-160-PPV End cap	Not available separately, see position 21	1	PC
21	8193965	DSBG-160-PPV End cap module		1	PC
22	684474	LUB-KC1 SILIKONFREI 20ML Lubricating grease		2	PC
23	8181257	CYBERBOND TM44 TB3ML Adhesive bonding agent		1	PC