

INB 2-25 - Insertion bridge



3251212

<https://www.phoenixcontact.com/fr/products/3251212>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insertion bridge, Bridging in the terminal point, number of positions: 2, color: gray



Commercial data

Item number	3251212
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BEKZ2X
Product key	BEKZ2X
GTIN	4046356951180
Weight per piece (including packing)	78.99 g
Weight per piece (excluding packing)	78.99 g
Customs tariff number	85389099
Country of origin	DE

INB 2-25 - Insertion bridge

3251212

<https://www.phoenixcontact.com/fr/products/3251212>



Technical data

Product properties

Number of positions	2
---------------------	---

Material specifications

Color	gray (RAL 7042)
Material	Cu
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

INB 2-25 - Insertion bridge

3251212

<https://www.phoenixcontact.com/fr/products/3251212>



Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 9.0	EC000489
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

INB 2-25 - Insertion bridge

3251212

<https://www.phoenixcontact.com/fr/products/3251212>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT SAS
52 Boulevard de Beaubourg Emerainville
77436 Marne La Vallée Cedex 2 France
+33 (0) 1 60 17 98 98
documentation@phoenixcontact.fr