

M100

14" 12"

6,7 Kg

98

art.		
024500100	M100	soft thermoformed tray with tool assortment
024510104	MV104	Tray M100, empty



- n. 1 **895/1**: socket holder
- n. 1 **895/3**: socket holder
- n. 1 **895/6**: socket holder
- n. 13 **900**: 1/4" hexagon sockets ○ 4 - 4,5 - 5 - 5,5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 mm
- n. 9 **900L**: hexagon hand sockets, long series ○ 5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 mm
- n. 5 **900ME**: 1/4" socket drivers for hexagon screws ○ 3-4-5-6-7 mm
- n. 4 **900LP**: 1/4" socket drivers for slotted head screws ● 0,8x4 - 1x5,5 - 1,2x6,5 - 1,2x8 mm
- n. 4 **900PH**: 1/4" socket drivers for cross head Phillips® screws ⬤ PH1-PH2-PH3-PH4
- n. 7 **900TX**: socket drivers for Torx® head screws ⬤ T10 - T15 - T20 - T25 - T27 - T30 - T40
- n. 1 **900/20**: 1/4" drive extension bar 50 mm
- n. 1 **900/20L**: 1/4" drive extension bar 100 mm
- n. 1 **900/21**: 1/4" drive extension bar 150 mm
- n. 1 **900/25**: 1/4" drive universal joint
- n. 1 **900BG/30**: 1/4" drive spinner handle
- n. 1 **900/42**: 1/4" drive swivel T-handle
- n. 1 **900/55**: 1/4" reversible ratchet ⚙
- n. 21 **920A**: 1/2" square drive hexagon sockets ○ 8-10-11-12-13-14-15-16-17-18-19-20-21-22-23-24-26-27-28-30-32 mm
- n. 1 **920/15**: adaptor, 1/2" female and 3/8" male drives
- n. 1 **920/25**: 1/2" drive universal joint
- n. 1 **920AN/125**: 1/2" wobble extension bar 125 mm
- n. 1 **920AN/250**: 1/2" wobble extension bar 250 mm
- n. 1 **920/42**: 1/2" drive sliding T-handle
- n. 1 **920/55**: 1/2" reversible ratchet ⚙
- n. 8 **920FTX**: 1/2" sockets for Torx® head screws ⬤ 10 - 12 - 14 - 16 - 18 - 20 - 22 - 24 mm
- n. 11 **920AL**: hexagon hand sockets ○ 10 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22

