



PROFIBOX, 100 SCHUKO sockets and 100 SCHUKO covers with Shutters Titan White

Model	
product brand name	DELTA
product designation	SCHUKO socket outlet
cover version	central plate
design of the special power supply unit	without special current supply
design of the socket according to VDE 0620 for severe conditions	No
design of the phase tap	No
General technical data	
marking of socket outlet	without imprint
mounting type	fixing with claw and screw
surface processing	others
material	thermoplastic
Supply voltage	
operating voltage rated value	250 V
supply voltage frequency rated value	50 Hz
Protection class	
protection class IP	IP20
Main circuit	
operational current rated value	16 A
Appearance	
color	titanium white
Product details	
product component	
• ejection equipment	No
• labeling field	No
• increased touch protection	Yes
• residual current device	No
• miniature fuse	No
• integrated functional lighting	No
• integrated light source	No
• integrated orientation lighting	No
• hinged lid	No
product feature	
• lockable	No
• halogen-free	Yes
• transparent	No
Product function	
product function	
• socket selectable	No

● overvoltage protection	No
<b>Number</b>	
number of units	1
number of sockets switchable	0
<b>Connections</b>	
arrangement of contacts diagonal	No
type of electrical connection	plug terminal
<b>Mechanical Design</b>	
height	500 mm
width	400 mm
depth	200 mm
fastening method	flush mounting
material of the enclosure	plastic
<b>Further information</b>	
Information on the packaging <a href="https://support.industry.siemens.com/cs/ww/en/view/109813875">https://support.industry.siemens.com/cs/ww/en/view/109813875</a> Information- and Downloadcenter (Catalogs, Brochures,...) <a href="http://www.siemens.com/lowvoltage/catalogs">http://www.siemens.com/lowvoltage/catalogs</a> Industry Mall (Online ordering system) <a href="https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5UB1518-0KA">https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5UB1518-0KA</a> Service&Support (Manuals, Certificates, Characteristics, FAQs,...) <a href="https://support.industry.siemens.com/cs/ww/en/ps/5UB1518-0KA">https://support.industry.siemens.com/cs/ww/en/ps/5UB1518-0KA</a> Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) <a href="http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5UB1518-0KA">http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5UB1518-0KA</a> CAx-Online-Generator <a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a> Tender specifications <a href="http://www.siemens.com/specifications">http://www.siemens.com/specifications</a>	

last modified:

5/26/2025 

