

Features

- For maintenance and general workshop use
- Durable coating and excellent mineral retention means long product life
- Easy to tear backing leaves clean and straight edges
- J-weight cloth gives enhanced flexibility without mineral loss and minimal surface cracking

RS PRO Emery Roll Range

RS Stock No.: 0757812



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Emery Roll

RS PRO industrial quality Emery Rolls range in handy, easy to use brand new dispenser packaging. Premium quality aluminium oxide grain bonded to strong yet easy to tear J-weight cloth backing. Designed for general maintenance work, rust removal, sanding and polishing. Popular for use in the automotive industry.

- *Suitable for use on Rust, Metal, Paint & Non Ferrous*
- *Popular for use in the automotive industry*
- *Premium quality aluminium oxide grain*

General Specifications

Abrasive Material	Aluminium Oxide
Sandpaper Type	Emery Cloth Roll
Grit Size	See details below
Grade	See details below
Length	See details below
Width	See details below

Stock No.	Grit Size	Grade	Length	Width
XXX-XXXX 0757806	60	Coarse	50M	38mm
XXX-XXXX 0757808	80	Medium Coarse	50M	38mm
XXX-XXXX 0757809	120	Medium	50M	38mm
XXX-XXXX 0757811	180	Fine	50M	38mm
XXX-XXXX 0757812	280	Very Fine	50M	38mm
XXX-XXXX 0757814	60	Coarse	50M	50mm
XXX-XXXX 0757815	80	Medium Coarse	50M	50mm
XXX-XXXX 0757816	120	Medium	50M	50mm
XXX-XXXX 0757817	180	Fine	50M	50mm
Stock No.	Grit Size	Grade	Length	Width
XXX-XXXX	280	Very Fine	50M	50mm

0757818				
XXX-XXXX 0757806	60	Coarse	50M	50mm

Approvals

Declarations	REACH DoC
---------------------	-----------

Similar Products

Stock No.	Brand	Product Name	Grit Size	Grade	Length	Width
XXX-XXXX 0757806	RS PRO	Emery Roll	60	Coarse	50M	38mm
XXX-XXXX 0757808	RS PRO	Emery Roll	80	Medium Coarse	50M	38mm
XXX-XXXX 0757809	RS PRO	Emery Roll	120	Medium	50M	38mm
XXX-XXXX 0757811	RS PRO	Emery Roll	180	Fine	50M	38mm
XXX-XXXX 0757812	RS PRO	Emery Roll	280	Very Fine	50M	38mm
XXX-XXXX 0757814	RS PRO	Emery Roll	60	Coarse	50M	50mm
XXX-XXXX 0757815	RS PRO	Emery Roll	80	Medium Coarse	50M	50mm
XXX-XXXX 0757816	RS PRO	Emery Roll	120	Medium	50M	50mm
XXX-XXXX 0757817	RS PRO	Emery Roll	180	Fine	50M	50mm
XXX-XXXX 0757818	RS PRO	Emery Roll	280	Very Fine	50M	50mm
XXX-XXXX 0757806	RS PRO	Emery Roll	60	Coarse	50M	50mm