



Einhell

PROFESSIONAL



Cordless Impact Driver

TP-CI 18/250-C Li BL - Solo

Item No.: 4510095

Ident No.: 21014

Bar Code: 4006825680379

The Einhell Professional Cordless Impact Driver TP-CI 18/250-C Li BL-Solo is a powerful member of the Power X-Change family. Powered by an Einhell Brushless Motor for increased power and longer runtime, it includes a 10-year motor warranty upon online registration. Designed for efficiency, it is compact, lightweight, and easy to handle. Torque and speed are adjustable in three stages to suit various applications. The driver features a 1/4" (6.35 mm) internal hexagon tool holder and an LED light for illuminating the work area. Delivered without battery and charger.

Features & Benefits

- Member of the Power X-Change family, 1x 18 V battery required
- Brushless motor - more power and longer running time
- Brushless - 10-year motor warranty after registration
- Compact and powerful
- 3 stages for optimum adjustment of torque and speed
- Special impact mechanism protects wrist from torsional forces
- Finely adjustable speed electronics for sensitive working
- LED light to illuminate the work area
- Quick-Stop for quick and easy tool changes
- Robust 1/4 inch hexagon socket
- Ergonomic shape with soft grip surfaces for optimum hold
- Belt clip for easy temporary storage
- Supplied without battery and charger (sold separately)



Technical Data

- | | |
|-------------------------|---------------------------|
| - Idle speed | 2800 min ⁻¹ |
| - Type of bit interlock | Mechanic locking sleeve |
| - tool collet (hex) | Bit holder (6,35 mm/1/4") |
| - Max. torque hard | 250 Nm |



COMPACT




3 SPEED SETTINGS



NO RECOIL

Logistic Data

- | | |
|--------------------------------------|--------------------|
| - Product weight (kg) | 0.95 |
| - Gross weight (kg) | 1.34 |
| - Pieces per export carton | 6 Pieces |
| - Gross weight export carton | 8.73 kg |
| - Dimensions Export Carton | 312 x 290 x 245 mm |
| - Container quantity (20"/40"/40"HC) | 7578 15696 |



Available as special accessories



Handy Bitbox Impact 12tlg.
Akku-Bohrschrauber-Zubehör
Item No.: 49155025
Bar Code: 4009311550255
Einhell Accessory



5,2 Ah Power X-Change Plus
Battery
Item No.: 4511437
Bar Code: 4006825616606
Einhell Accessory



PXC 18V 3,0Ah
Battery
Item No.: 4511341
Bar Code: 4006825590593
Einhell Accessory



3,0 Ah Power X-Change Plus
Battery
Item No.: 4511501
Bar Code: 4006825644197
Einhell Accessory



2,0 Ah Power X-Change
Battery
Item No.: 4511395
Bar Code: 4006825610369
Einhell Accessory



4,0 Ah Power X-Change
Battery
Item No.: 4511396
Bar Code: 4006825610376
Einhell Accessory



4-6 Ah Multi-Ah Power X-Change
Plus
Battery
Item No.: 4511502
Bar Code: 4006825644210



2x18V 4,0Ah PXC-Twinpack CB
B1
Battery
Item No.: 4511489
Bar Code: 4006825638578



2x2 Power X-Quattrocharger 4A
Charger
Item No.: 4512102
Bar Code: 4006825649536
Einhell Accessory



Power X-Fastcharger 4A
Charger
Item No.: 4512103
Bar Code: 4006825650228
Einhell Accessory



Power X-Twincharger 3A
Charger
Item No.: 4512069
Bar Code: 4006825629729
Einhell Accessory



Power X-Car Charger 3A
Charger
Item No.: 4512113
Bar Code: 4006825655377
Einhell Accessory



18V 2,5Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512097
Bar Code: 4006825646962
Einhell Accessory



18V 2,0Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512040
Bar Code: 4006825613681
Einhell Accessory



18V 4,0Ah PXC Starter Kit B1
PXC-Starter-Kit
Item No.: 4512042
Bar Code: 4006825613704
Einhell Accessory

Battery-Running-Times



screwing¹
(pieces)

One Battery for All

One Battery for All	screwing ¹ (pieces)
1.5 Ah	195
2.0 Ah	265
2.5 Ah	330
3.0 Ah	390
4.0 Ah	530
5.2 Ah	680
6.0 Ah	780
8.0 Ah	1060

Test setup:

1) screws - 6x60 mm