



Insulated food liner with Cut F protection for cold food handling environments.

**TEGERA® 918**



[Learn more](#)

**CUT F FOR FOOD CONTACT WITH EXTRA THICKNESS**

This food-approved Cut F liner offers high cut protection. The soft brushed acrylic interior provides warmth and comfort when working with cold food items. Built with TEGERA® CRF® Technology for durable cut resistance and fingertip sensitivity. Washable at 90 °C/194 °F and suitable for repeated use. Designed for use under disposable gloves in cold food processing environments.

**CHARACTERISTICS**

- Good fingertip sensitivity
- Flexible
- Comfortable
- Warm

**FUNCTIONS**

- Approved for handling foodstuffs
- Extra long
- Soft
- Washable in 90° C



**PREVENTS RISK OF**

Cut injuries, Scratches, lacerations, Contact with cold

**PRIMARY ENVIRONMENTS OF USE**

Cut risk environments, Dry environments, Cold environments

**PRIMARY AREAS OF USE**

Fishing industry work, Food handling, Hotel- and restaurant work, Kitchen work

**PRIMARY INDUSTRIES OF USE**

Food processing

**TYPE OF WORK**

Heavy weight

**SPECIFICATION**

**TYPE** Cold insulation gloves, Cut resistant gloves

**CATEGORY** Cat. II

**KNITTING GAUGE (GG)** 10

**LINING MATERIAL** Acrylic, CRF® Technology, HPPE, Polyester, Spandex, Stainless steel fibre yarn

**LENGTH** 210-325 mm

**DEXTERITY** 3

**COLOUR** Blue

**PAIRS PER: BUNDLE/CARTON** 10/60

**DISPLAY TYPE** Bulk pack

**CUFF STYLE** Extended knitwrist cuff

**CUFF MATERIAL** Textile

**CUT RESISTANCE (EN ISO 13997)** Cut resistance level F

**CUT RESISTANCE (EN ISO 13997) TDM:** 37N

**OUTER MATERIAL SPECIFICATION** Acrylic, HPPE (High performance polyethylene), Stainless steel fibre yarn, Polyester, Elastane

**COMPLIANCE**



EN ISO 21420:2020



TP TC 019:2011



EN 388:2016+A1:2018 1X4XF



Wash once before use for best fit

Maximum 5 wash cycles at 90°C

**FEATURES**



Cut protection



Warm lining



Washable 90°C

SIZE		ARTICLE NUMBER	EAN
10	XL	918-10	7333506016620
11	XXL	918-11	7333506016774
12	3XL	918-12	7333506016927
5	XXS	918-5	7333506017108
6	X5	918-6	7333506016026
7	S	918-7	7333506016170
8	M	918-8	7333506016323
9	L	918-9	7333506016477

**ejendals**

Limavägen 28, SE-793 32 Leksand, Sweden

Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com