

# WP-OR PG29 - Sealing ring

3241199

<https://www.phoenixcontact.com/gb/products/3241199>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sealing ring, for threads Pg29, color: black



## Your advantages

- The properties of the Perbunan O-rings, such as their resistance to oil and seal against water and dust, mean that they can be used in a wide range of applications

## Commercial data

Item number	3241199
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	AF7DSA
Product key	AF7DSA
Catalog page	Page 607 (C-3-2019)
GTIN	4046356786058
Weight per piece (including packing)	0.512 g
Weight per piece (excluding packing)	0.504 g
Customs tariff number	40169300
Country of origin	DE

# WP-OR PG29 - Sealing ring

3241199

<https://www.phoenixcontact.com/gb/products/3241199>



## Technical data

### Product properties

Product type	Seal
Thread type	Pg29

### Dimensions

Height	2 mm
Thread type connection side	Pg29

### Internal dimensions

Internal diameter	34 mm
-------------------	-------

### Material specifications

Material	Perbunan
----------	----------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 120 °C
---------------------------------	-------------------

# WP-OR PG29 - Sealing ring



3241199

<https://www.phoenixcontact.com/gb/products/3241199>

## Classifications

### ECLASS

ECLASS-13.0	27430319
-------------	----------

### ETIM

ETIM 9.0	EC001181
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# WP-OR PG29 - Sealing ring

3241199

<https://www.phoenixcontact.com/gb/products/3241199>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)