

Barcode Labels and Supplies for WPL205 & WPL305



WPL205 & WPL305 BARCODE LABELS - Direct Thermal Quad Packs

MFG#	Desc (WxL)	Roll O.D.	Labels/Roll	Rolls/Pack
633808402686	1.25" x 1.0"	5"	2300	4
633808402693	1.5" x 1.0"	5"	2300	4
633808402709	2.0" x 1.0"	5"	2300	4
633808402716	2.25" x 0.75"	5"	3000	4
633808402723	2.25" X 1.25"	5"	1900	4
633808402730	3.0" X 3.0"	5"	850	4
633808402747	3.5" x 1.0"	5"	2300	4
633808402754	4.0" x 1.0"	5"	2300	4
633808402761	4.0" x 2.0"	5"	1250	4
633808402778	4.0" x 3.0"	5"	850	4
633808402785	4.0" x 6.0"	5"	450	4



WPL305 BARCODE LABELS - Thermal Transfer Quad Packs (Ribbon Required)

MFG#	Desc (WxL)	Roll O.D.	Labels/Roll	Rolls/Pack
633808402488	1.25" x 1.0"	5"	2300	4
633808402495	1.5" x 1.0"	5"	2300	4

633808402501	2.0" x 1.0"	5"	2300	4
633808402518	2.25" x 0.75"	5"	3000	4
633808402525	2.25" X 1.25"	5"	1900	4
633808402532	3.0" X 3.0"	5"	850	4
633808402549	3.5" x 1.0"	5"	2300	4
633808402556	4.0" x 1.0"	5"	2300	4
633808402563	4.0" x 2.0"	5"	1250	4
633808402570	4.0" x 3.0"	5"	850	4
633808402587	4.0" x 6.0"	5"	450	4



Wasp Wax - WWX Wax Barcode Ribbon

WWX ribbon is a general purpose ribbon particularly adapted to standard label printing where good mechanical resistance is required. The ink provides an excellent print quality of picket and ladder barcodes, very small text, large characters, and logos.

The ribbon structure allows printing on various label stock, such as coated and uncoated papers, and some synthetics. The printed ink offers improved smudge resistance compared to standard wax, and heat resistance up to 65°C (149°F).

These characteristics remain at speeds up to 300mm/s (12 ips), and with 200, 300 and 600 DPI printheads. WWX features Wasp's outstanding backcoat technology ensuring excellent printhead protection, no clogging and prevents static build up.

MFG#	Desc (WxL)	Formula
633808431136	WWX 1.57" x 820'	Wax
633808431143	WWX 2.16" x 820'	Wax
633808431150	WWX 3.26" x 820'	Wax
633808431167	WWX 4.33" x 820'	Wax



Wasp Premium - WPR Wax-Resin Barcode Ribbon

WPR ribbon combines a multi label stock compatibility with a good level of performances. This high versatility allows it to fulfill the requirements of many applications. The ink provides an excellent printing quality of all types of barcodes, very small text, large characters, and logos.

The ribbon structure allows printing on various kinds of label stock, such as uncoated papers, coated papers, and synthetics. The printed image offers a good level of smudge resistance, and heat resistance up to 100°C (212°F).

Those characteristics remain at speeds up to 300mm/s (12 ips), and with 200, 300 and 600 DPI printheads, making this ribbon perfectly adapted either to the labeling market or the flexible packaging printing market. WPR features Wasp's outstanding backcoat technology ensuring excellent printhead protection, no clogging, prevents static buildup.

MFG#	Desc (WxL)	Formula
633808431174	WPR 1.57" x 820'	Wax/Resin

633808431181	WPR 2.16" x 820'	Wax/Resin
633808431198	WPR 3.26" x 820'	Wax/Resin
633808431204	WPR 4.33" x 820'	Wax/Resin



Wasp eXtra - WXR Resin Barcode Ribbon

WXR ribbon is dedicated to applications requiring a perfect printing quality and excellent mechanical resistances. The ink provides excellent print quality of all types of barcodes, very small text, large characters, and logos.

The ribbon structure allows printing on many kinds of synthetics (PVC, PET, PE, PP), on various matte and high gloss coated papers and even on some uncoated papers. The printed image offers an excellent smudge and scratch resistance, and good heat resistance, up to 180°C (356°F).

Those characteristics remain at speeds up to 250mm/s (10 ips), and with 200, 300 and 600 DPI printheads, making this ribbon perfectly suited to the labeling market, and allowing its use in the flexible packaging printing market.

WXR features Wasp's outstanding backcoat technology ensuring excellent printhead protection, no clogging, and prevents static buildup.

MFG#	Desc (WxL)	Formula
633808431211	WXR 1.57" x 820'	Resin
633808431228	WXR 2.16" x 820'	Resin
633808431235	WXR 3.26" x 820'	Resin
633808431242	WXR 4.33" x 820'	Resin