

FOCUSED ON FEATURES FOR TODAY'S WORKERS.



PowerForm[®] Black

POWDER-FREE BIODEGRADABLE NITRILE EXAM GLOVES

Previously known as Stellar S6

Tested and certified for protection against viruses (EN ISO374-5)


PROTECT HANDS—AND THE ENVIRONMENT—WITH A BIODEGRADABLE SINGLE-USE GLOVE THAT COMBINES PERFORMANCE, DURABILITY AND TACTILE SENSITIVITY FOR CRITICAL TASKS.

- EcoTek[®] Biodegradability Technology accelerates landfill breakdown without any performance loss
- Consistent thickness for greater dexterity and tactile sensitivity
- Fully textured for excellent wet and dry grip
- Silicone-free for critical environments
- Clean processing technology reduces potential skin irritation
- Optimal thickness for durability and tactile sensitivity
- Tear-resistant beaded cuff eases donning
- 1.5 AQL exceeds laboratory standards

PF

WEIGHT	LENGTH	THICKNESS	FEATURES	COLOR
 6.5g (large size)	 9.0"	 5.0 mil	EcoTek [®]	BLACK

EcoTek



EcoTek[™]
BIODEGRADABLE



SafetyMate

TECHNICAL DATA

PowerForm® Black

POWDER-FREE BIODEGRADABLE NITRILE EXAM GLOVES

PRODUCT DESCRIPTION

SPECIFICATIONS

PRODUCT	PowerForm®	
GRADE	Powder-Free Exam	
MATERIAL	Nitrile	
THICKNESS	FINGER	5.6mil 0.14mm
	PALM	5.0mil 0.13mm
COLOR	Black	
SURFACE	Fully Textured	
LENGTH	9.0"	229mm
WEIGHT	6.5g	
FIT TYPE	Ambidextrous	
CUFF TYPE	Beaded	
WATERTIGHT AQL	1.5	
ORIGIN COUNTRY	China	

* Specifications based on size Large glove

PHYSICAL PROPERTIES

	PRE-AGING	POST-AGING
TENSILE		
STRENGTH:	22 MPA	20 MPA
ELONGATION:	540%	520%

INTEGRATED TECHNOLOGIES

ECOTEK® Biodegradability Technology: 92.6% biodegradable in 2.5 years. ASTM D5526-12 test results do not predict future biodegradation.


100% Air Inspected

Clean Washed



STANDARDS & CERTIFICATIONS

EN 420-2003 FDA 21 CFR 177.2600
 REACH EU 1907/2006
 EU 2016/425
 CAT III COMPLEX DESIGN
 TGA LISTED (ARTG# 334926)



Please visit swsafety.com/symbols for information on standards used on this document.

APPLICATIONS

Chemical Handling
 Dairy
 Painting
 Tattooing and Cosmetics

ORDERING

Item No.	Size	Palm Width	Packaging
N716882	S 6½ – 7	3.5" 89mm	100 gloves per box 10 boxes per case
N716883	M 7½ – 8	3.8" 98mm	100 gloves per box 10 boxes per case
N716884	L 8½ – 9	4.3" 108mm	100 gloves per box 10 boxes per case
N716885	XL 9½ – 10	4.6" 116mm	100 gloves per box 10 boxes per case
N716886	2XL 10½ – 11	5.0" 126mm	100 gloves per box 10 boxes per case

STORAGE

Keep out of sunlight. Store in a cool, dry place. Keep away from sources of ozone or ignition.



EcoTek™
 BIODEGRADABLE

FINALLY. BIODEGRADABILITY WITHOUT PERFORMANCE LOSS.

Ecotek is a nitrile treatment that accelerates the break-down in landfills without performance loss. Ecotek gloves biodegrade in landfill, 92.6% in 2 ½ years tested according to ASTM D5526-12. SW is changing the future of disposable gloves with Ecotek, an innovative solution that contributes to a cleaner environment for a better tomorrow.

R_N71688X0919

