

Reciprocating Saw LXT®

DJR183

18V • 0 – 3 000 min⁻¹ • 13 mm

Compact reciprocating saw for light use

A straight-framed light and small reciprocating saw offers access to tight places. Two separate switches enable diverse working postures. Stroke length of 13 mm, stroke rate can be adjusted between 0 – 3 000 min⁻¹ from a switch. LED light and quick-release blade attachment.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Strokes per Minute (SPM)	0 - 3000 min ⁻¹
Length of Stroke	13 mm
Max. Cutting Capacity in Wood (90°)	50 mm
Max. Cutting Capacity in Steel Pipe	50 mm
Sound Power Level (L _{WA})	88 dB(A)
Sound Pressure Level (L _{pA})	80 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,5 - 1,8 kg
Product Dimensions (L x W x H):	398 x 81 x 220 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Vibration Level, Cutting Boards	8,0 m/s ²
Vibration Uncertainty (K Factor), Cutting Boards	1,5 m/s ²

User benefits

- Tool-less blade change and shoe adjustment
- Compact and lightweight design
- Two different operating switches for versatile working
- LED light illuminates the work site
- Ideal for working in tight spaces and overhead applications
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.dk



Related products

Optional AC

450128-8

Battery cover, LXT®, 14,4 – 18V

821550-0

Makpac case (2)

B-03030

Reciprosaw Blade 300 x 1,25 mm

B-10394

Reciprosaw Blade 305 x 1,5 mm

B-20395

Reciprosaw Blade 100 x 0,9 mm

B-20410

Reciprosaw Blade 100 x 0,9 mm

B-31859

Reciprosaw Blade 225 x 0,9 mm

B-44448

Reciprosaw Blade Set 6 pcs

P-04927

Reciprosaw Blade 200 x 0,9 mm

P-04949

Reciprosaw Blade 200 x 0,9 mm

P-05016

Reciprosaw Blade 300 x 1,4 mm

P-05044

Reciprosaw Blade 150 x 1,3 mm

P-05088

Reciprosaw Blade 150 x 1,5 mm

P-47189

Reciprosaw Blade 150 x 1,27 mm



783201-2

Hex Wrench 3Mm



837897-2

MakPac Type 2 Inner Tray



B-05153

Reciprosaw Blade 203 x 1,0 mm



B-10403

Reciprosaw Blade 455 x 1,5 mm



B-20404

Reciprosaw Blade 100 x 0,9 mm



B-20432

Reciprosaw Blade 100 x 0,9 mm



B-44432

Reciprosaw Blade Set 6 pcs



P-04880

Reciprosaw Blade 150 x 1,4 mm



P-04933

Reciprosaw Blade 200 x 0,9 mm



P-04983

Reciprosaw Blade 280 x 0,9 mm



P-05022

Reciprosaw Blade 150 x 1,3 mm



P-05072

Reciprosaw Blade 300 x 1,2 mm



P-45680

Reciprosaw Blade 150 x 0,9 mm



P-47195

Reciprosaw Blade 225 x 1,27 mm

Other

User manual

Parts drawing