

Product datasheet

Specifications

Cable gland SNAP-IN quick fixing M40, polyamide IP68 UV resistant



NSYCGSP40

EAN Code: 3606481360373

Main

Range	PanelSeT
Product or component type	Cable gland
Accessory / separate part category	Cable management accessory
Range compatibility	Thalassa Thalassa PLM PanelSeT PanelSeT S3D PanelSeT PanelSeT S3X
Mounting location	Enclosure top Enclosure bottom
Cable entry	Cable gland M40
Device composition	1 cable gland 1 seal
Quantity per set	Set of 5
Material	Seal: CR (chloroprene) Body: PA (polyamide) 6

Complementary

Colour	Grey (RAL 7035)
Fixing mode	Push and turn clockwise
Net weight	0.066 kg

Environment

Product certifications	VDE
Environmental characteristic	UV resistant
Flame retardance	V2 conforming to UL 94
Ambient air temperature for operation	-20...100 °C permanent -30...150 °C intermittent
IP degree of protection	IP68 conforming to IEC 60529 5 bar, 30 min

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	5.000 cm
Package 1 Length	5.000 cm
Package 1 Weight	66.000 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	6.000 cm
Package 2 Width	16.000 cm
Package 2 Length	19.000 cm
Package 2 Weight	340.000 g
Unit Type of Package 3	CAR
Number of Units in Package 3	10
Package 3 Height	11.000 cm
Package 3 Width	19.000 cm
Package 3 Length	19.000 cm
Package 3 Weight	786.000 g

Logistical informations

Country of origin	TR
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)

Use Again

 Repack and remanufacture	
Take-back	No