



Combinations for connectors in Gel filled boxes

Material	Colour	Material	Colour	Material	Colour	Material	Colour	Material	Colour	Material	Colour	Material	Colour	Material	Colour	Material	Colour	Material	Colour	
Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green
Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green
Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green	Green

## SCP-23 0525

E1441434

Branch Connector 2-Pole, 3-Conductors/Pole, 0.5-2.5mm<sup>2</sup>



### Product Properties:

Number of clamp positions (device side)	6 .
Type of locking/unlocking	Lever
Nominal voltage	450 V
Nominal current	25 A
Suitable for solid conductors	Yes
Transparent	Yes
Number of clamp positions	6 .
With operation lever	Yes
Suitable for solid core	Yes
Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Strip length	12 mm
Colour	Multi-coloured
Operating temperature	-40-105 °C
Flammability rating (UL94)	V2

### Dimensions:

Max. AWG-size	12
Min. AWG-size	24
Nominal cross section (device side)	0.5-2.5 mm <sup>2</sup>
Nominal cross section (installation side)	0.5-2.5 mm <sup>2</sup>
Cable diameter	1-4 mm

Conductor cross section flexible (fine-strand) with cable end sleeve	0.5-2.5 mm <sup>2</sup>
Conductor cross section solid (solid, stranded)	0.5-4 mm <sup>2</sup>
Width	25.2 mm
Height	11.1 mm
Strip length	12 mm
MOQ	20 .
Unit	pcs
Nominal cross section	0.5-2.5 mm <sup>2</sup>
Length	30 mm
Nominal voltage	450 V

### **Approvals:**

Approved according to CE	Yes
Approved according to TUV	Yes
Approved according to UKCA	Ja

### **Compliance:**

Conflict Minerals	N/A, Contains no conflict minerals
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)

### **Other information:**

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	102016
Search Description	ENR2025H, ENR2025H, EFO2025H, SKH2025MK, E0812903
Alternative SKU	SCP-230525
E-no	E1441434

### **Logistic information:**

Barcode	733117642925
Country of origin	CN
E-no	E1441434
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	20 .
Stock code	SCP-23 0525
Taric code	85369010
Unit	pcs

\*We reserve the right to make technical changes and disclaim any typographical errors.

---

**Nelco Contact AB** - Daléns Gata 7, 195 61 Arlandastad, Sweden - Tel. +46 (0)8 754 70 40 - [order@nelco.se](mailto:order@nelco.se) - [www.nelco.se](http://www.nelco.se)