

PRODUCT-DETAILS

TY53510MX

CABLE TIE 175LB 35IN UV BLACK NYLON



General Information

Extended Product Type	TY53510MX
Product ID	7TCG009380R0002
EAN	5414363066125
Catalog Description	CABLE TIE 175LB 35IN UV BLACK NYLON
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/215 Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 889mm (35.0 Inches), Width of 8.13mm (0.32 Inches), Thickness of 1.7mm (0.07 Inches), Tensile Strength Rating of 780 Newtons (175 pounds)

Ordering

EAN	5414363066125
UPC	786210304816

Dimensions

Product Net Width	0.32 in 8.13 mm
Product Net Depth / Length	35 in 889 mm

Container Information

Package Level 1 Units	50 piece
Package Level 1 Width	1 in 25 mm
Package Level 1 Height	7 in 178 mm
Package Level 1 Depth / Length	40 in 1016 mm
Package Level 2 Units	250 piece
Package Level 2 Width	5.25 in 133 mm
Package Level 2 Height	6 in 152 mm
Package Level 2 Depth / Length	38 in 965 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	Max 10 in Max 254 mm
Color	Black
Effective Date	19950719
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	NYLON DUCT TIE
Product Type	High Performance
Special Functions	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Tensile Strength	175 lb 780 N
Thickness	0.07 in 1.7 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY53510MX
Instructions and Manuals	TY53510MX
REACH Declaration	9AKK107992A3994
RoHS Information	9AKK107991A8361

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

