

Design Kit Common Mode Chokes WE-LF

Order Code: 744630

Characteristics:

- Sample kit contains 36 components of the Current Compensated Chokes WE-LF
- Inductance values from 0.4 mH to 50 mH
- 8 types, 36 values and 72 components in one sample case
- Free refill



Electrical properties

Order Code	A (mm)	B (mm)	C (mm)	D (mm)	E (mm)	F (mm)	G (mm)	H (mm)	Inductance (mH)	Rated Current (A)	DC Resistance (Ω)	Operating Voltage	Coil Ratio	Design	Insulation Test Voltage	Description
7446120027	18.5	13.5	20.5		10.0	3.0	0.6	15.0	27	0.4	1.20	250 V AC	2	THT	1.5 kV AC	Current Compensated Power Line Choke WE-LF
7446120039	18.5	13.5	20.5		10.0	3.0	0.6	15.0	39	0.4	1.70	250 V AC	2	THT	1.5 kV AC	Current Compensated Power Line Choke WE-LF
7446120047	18.5	13.5	20.5		10.0	3.0	0.6	15.0	47	0.3	2.60	250 V AC	2	THT	1.5 kV AC	Current Compensated Power Line Choke WE-LF

7446121007	18.5	13.5	20.5		10.0	3.0	0.6	15.0	6.8	1.0	0.30	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WE-LF
7446121010	18.5	13.5	20.5		10.0	3.0	0.6	15.0	10	0.7	0.55	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WE-LF
7446122001	18.5	13.5	20.5		10.0	3.0	0.6	15.0	1.0	2.0	0.06	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WE-LF
7446122003	18.5	13.5	20.5		10.0	3.0	0.6	15.0	3.3	1.5	0.15	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WE-LF
74461240004	18.5	13.5	20.5		10.0	3.0	0.6	15.0	0.4	3.6	0.02	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WE-LF
7446620027	18.0	18.0	13.0	10.0	15.0	3.0	0.6		27	0.4	1.20	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WE-LF
7446621007	18.0	18.0	13.0	10.0	15.0	3.0	0.6		6.8	1.0	0.30	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WE-LF

7446622002	18.0	18.0	13.0	10.0	15.0	3.0	0.6	2.2	2.0	0.10	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
74466240007	18.0	18.0	13.0	10.0	15.0	3.0	0.6	0.7	4.0	0.03	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446220047	23.5	16.0	25.5	10.0	12.5	3.0	0.6	47	0.4	1.60	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446221010	23.5	16.0	25.5	10.0	12.5	3.0	0.6	10	1.3	0.25	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446221012	23.5	16.0	25.5	10.0	12.5	3.0	0.6	12	1.2	0.28	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446221027	23.5	16.0	25.5	10.0	12.5	3.0	0.6	27	0.6	0.70	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446222002	23.5	16.0	25.5	10.0	12.5	3.0	0.6	2.2	2.0	0.06	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF

7446222003	23.5	16.0	25.5	10.0	12.5	3.0	0.6	3.3	2.0	0.075	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446222004	23.5	16.0	25.5	10.0	12.5	3.0	0.6	4.2	2.0	0.12	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446223001	23.5	16.0	25.5	10.0	12.5	3.0	0.6	1.0	3.0	0.04	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
74462250007	23.5	16.0	25.5	10.0	12.5	3.0	0.6	0.7	4.7	0.02	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446720047	23.0	23.0	14.5	12.5	20.0	3.0	0.6	47	0.4	1.60	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446722002	23.0	23.0	14.5	12.5	20.0	3.0	0.6	2.2	2.0	0.06	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446722007	23.0	23.0	14.5	12.5	20.0	3.0	0.6	6.8	1.5	0.20	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF

7446321033	26.5	18.5	30.5	12.5	15.0	3.0	0.6	33	0.8	0.85	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446321050	26.5	18.5	30.5	12.5	15.0	3.0	0.6	50	0.6	1.20	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446322010	26.5	18.5	30.5	12.5	15.0	3.0	0.6	10	1.9	0.18	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446323003	26.5	18.5	30.5	12.5	15.0	3.0	0.6	2.7	3.0	0.06	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446323004	26.5	18.5	30.5	12.5	15.0	3.0	0.6	4.0	3.0	0.07	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446326002	26.5	18.5	30.5	12.5	15.0	3.0	0.6	1.8	6.0	0.02	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446821027	28.5	28.5	17.0	15.1	25.2	3.0	0.6	27	1.0	0.64	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF

7446822006	28.5	28.5	17.0	15.1	25.2	3.0	0.6	5.6	2.0	0.16	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446422007	32.5	21.5	35.5	12.5	17.5	5.0	0.8	6.8	2.5	0.120	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446424002	32.5	21.5	35.5	12.5	17.5	5.0	0.8	2.2	4.3	0.038	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446921027	33.5	33.5	20.0	20.1	30.2	3.5	0.8	27	1.2	0.40	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF
7446926002	33.5	33.5	20.0	20.1	30.2	3.5	0.8	1.8	6.0	0.03	250 V AC 2	THT	1.5 kV AC	Current Compensated Power Line Choke WELF

Subject to changes