

# ZB 5,QR:FORTL.ZAHLEN 81-90 - Zack marker strip



1050020:0081

<https://www.phoenixcontact.com/pc/products/1050020:0081>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, 10-section, vertically labeled with the consecutive numbers: 81 ... 90, white, for terminal block width: 5.2 mm, mounting type: latching

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1050020:0081  |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Product key                          | BG2122        |
| GTIN                                 | 4017918507787 |
| Weight per piece (including packing) | 1.36 g        |
| Weight per piece (excluding packing) | 1.066 g       |
| Customs tariff number                | 49119900      |
| Country of origin                    | DE            |

1050020:0081

<https://www.phoenixcontact.com/pc/products/1050020:0081>

## Technical data

### Product properties

|       |        |
|-------|--------|
| Pitch | 5.2 mm |
|-------|--------|

### Marking

|           |           |
|-----------|-----------|
| Printing  | 81 ... 90 |
| Slot type | high      |

### Mounting

|               |          |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

### Material specifications

|  |                                |
|--|--------------------------------|
| Color                                  | white (RAL 9010)               |
| Material                               | PA                             |
| Flammability rating according to UL 94 | V2                             |
| Base element material                  | PA                             |
| Components                             | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)                     | -40 °C ... 100 °C   |
| Recommended ambient temperature (storage/transport) | 23 °C   |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |
| Shelf life  | 2 years   |

### Dimensions

|        |         |
|--------|---------|
| Width  | 5.15 mm |
| Height | 10.5 mm |
| Depth  | 4.20 mm |
| Pitch  | 5.2 mm  |

#### Text field

|                   |          |
|-------------------|----------|
| Text field width  | 5.15 mm  |
| Text field height | 10.50 mm |

### Standards and regulations

|                 |              |
|-----------------|--------------|
| Wipe resistance | DIN 30646    |
|                 | DIN VDE 0611 |

# ZB 5,QR:FORTL.ZAHLEN 81-90 - Zack marker strip



1050020:0081

<https://www.phoenixcontact.com/pc/products/1050020:0081>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstraße 8  
D-32825 Blomberg  
+49 (0) 5235-3 00  
[info@phoenixcontact.com](mailto:info@phoenixcontact.com)