

Warning label - PML-W300 (105X52)R - 0830460


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Warning label, Roll, yellow, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK X, Mounting type: Adhesive, Lettering field: 105 x 52 mm



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 717847
Weight per Piece (excluding packing)	99.99 g
Custom tariff number	39199000
Country of origin	Germany

Technical data

Dimensions

Length (b)	52 mm
Width (a)	105 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Ambient temperature (assembly)	> 8 °C
Recommended storage conditions	4 °C - 40 °C Storage in a cool and dark place in the original packaging is recommended.

General

Color	yellow
Type	Rectangle
Components	Silicone-free
Material	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	250
Number of individual labels per row	1

Warning label - PML-W300 (105X52)R - 0830460

Technical data

General

Adhesive	Acrylic
Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
	5146723 THERMOMARK ROLL X1
	5146257 THERMOMARK S1.1
	5146231 THERMOMARK X1.2
Ink ribbon	5145384 THERMOMARK-RIBBON 110
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	Following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Foil strength	50 µm
Marking mounting type	Adhesive

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

ETIM

ETIM 3.0	EC001694
ETIM 4.0	EC001777
ETIM 5.0	EC001777

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410

Warning label - PML-W300 (105X52)R - 0830460

Classifications

UNSPSC

UNSPSC 12.01	39121410
UNSPSC 13.2	39121410