

# Product data sheet

Specifications



## Repacked Wall box, Multifix, 1 gang box 67x50, polar white

IMT35915W



This repacked option saves 3.531 over the standard condition

### Main

|                           |               |
|---------------------------|---------------|
| Range                     | Multifix      |
| Product or component type | Wall box      |
| Device presentation       | Without cover |

### Complementary

|                 |                                                            |
|-----------------|------------------------------------------------------------|
| Number of gangs | 1 gang                                                     |
| fixing mode     | By screws and claws                                        |
| Colour tint     | Polar white                                                |
| Cable entry     | 2 knock-out diameter: 16 mm<br>2 knock-out diameter: 20 mm |
| Height          | 67 mm                                                      |
| Width           | 67 mm                                                      |
| Depth           | 50 mm                                                      |
| Diameter        | 67 mm                                                      |

### Environment

|                         |      |
|-------------------------|------|
| IP degree of protection | IP20 |
|-------------------------|------|

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 5.1 cm  |
| Package 1 Width              | 7.3 cm  |
| Package 1 Length             | 7.3 cm  |
| Package 1 Weight             | 22 g    |
| Unit Type of Package 2       | BB1     |
| Number of Units in Package 2 | 50      |
| Package 2 Height             | 18.3 cm |
| Package 2 Width              | 21 cm   |
| Package 2 Length             | 37.8 cm |
| Package 2 Weight             | 1.27 kg |
| Unit Type of Package 3       | P12     |
| Number of Units in Package 3 | 2500    |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                  |          |
|------------------|----------|
| Package 3 Height | 105 cm   |
| Package 3 Width  | 80 cm    |
| Package 3 Length | 120 cm   |
| Package 3 Weight | 84.45 kg |

## Contractual warranty

|                      |    |
|----------------------|----|
| Warranty (in months) | 18 |
|----------------------|----|



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Lower carbon footprint

4 kg CO2 eq.

## Use Better



### Materials and Substances

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Free of Substances of Very High Concern above the threshold](#)

## Use Longer



### Lifetime extension

Repair

No

## Use Again



### Repack and remanufacture

Take-back

No