

Freecom Classic SL Hard Drive USB-2



Stylish, cost effective external hard drive; the easy way to add extra GigaBytes to your computer

Freecom Classic SL Hard Drive

- Fast, low noise external USB-2 Hard Drive
- High quality aluminium enclosure, with optimal airflow management
- The easiest way to add and manage extra storage capacity to your computer
- Hot swappable, no need to turn off your computer
- No device ID's or terminations to worry about
- High quality, sleek design, only 215 x 115 x 30mm, easy to take with you
- Two years manufacturers warranty, free helpdesk support

Designed for:

- *Data storage*; use all your data, like business information and digital photos, videos, MP3s and all other files directly from the drive
- *File sharing*; share all your important data between computers and networks
- *Backup*; protect all your data against calamity, human errors and virus infections
- *Archiving*; archive all your data and lock up drive for extra data security
- *Installations*; copy all your software on multiple PCs

The most cost-effective Hi-Speed hard drive solution.

It's all about Gigabytes. Programs and data take up more and more storage space. The need for installing an extra harddrive on your PC is more present than ever. Freecom now offers the perfect upgrade for your PC: the Classic SL Hard Drive, a no-nonsense external hard drive. No need to open your PC: just plug the Classic SL Hard Drive in the USB port (USB 2.0 or 1.1) and you instantly have a substantial increase in storage space. The future is simple!



WWW.FREECOM.COM

Freecom
Keep it simple

Product specifications	Freecom Classic SL Hard Drive USB-2
Storage capacity	80GB, 120GB, 160GB, 250GB, 320 GB, 400GB, 500GB
Interface	USB 2.0 (1.1) supports transfer rates of up to 480Mbit/s.
Performance	Average seek time: <9 ms Track to Track seek time: 0.8 ms Average Latency: 4.2 ms
Data Transfer Speed	over USB 2.0 bus: up to 480Mbit/s over USB 1.1 bus: up to 12Mbit/s
Hard drive Buffer Size	2MB (400GB: 8MB)
MTBF	50000 P.O.H.
Physical specifications	215 x 115 x 30mm / 8.5 x 4.5 x 1.2 inch - Weight 750 gr. / 26.5 Ounce
Environmental specifications	Operating Temperature 5° C to 55° C Storage Temperature -40° C to 65° C
System Requirements:	PC: Pentium-II 233MHz or higher, 64MB RAM, CD-ROM drive Windows 98SE/ME/2000/XP Available USB port (USB 2.0 or USB 1.1) Internet access for latest driver download, online manual and online warranty registration MAC OS X or higher
Power Requirements	Voltage Adapter 200~240VAC, power ON-OFF switch
Package includes:	<ul style="list-style-type: none"> • Classic SL Hard Drive USB-2 • Power Adapter • USB cable (USB 2.0 & 1.1) • Freecom Software Media Suite • Manual on CD • Quick Install Guide • Free help desk support • Two years manufacturers warranty
Optional	<ul style="list-style-type: none"> • Freecom USB 2.0 PCI host controller 2-ports

Freecom Software Media Suite includes:**Freecom Secure & Compress for Windows:** Drag and drop files into folders and these files are encrypted and compressed automatically.**Freecom Password protection:** Protects your Classic drive with password protection.**Freecom Auto Run for Windows:** Opens files, starts programs automatically if you connect your Freecom Classic to the USB port.**Freecom Sync for Windows:** A synchronization process starts automatically if you connect your Freecom Classic to your computer.

	80GB	120GB	160GB	250GB	320GB	400GB	500GB
Art. No. EU/UK	24934	24935	24936	24937	24938	24939	25913
EAN code EU/UK	4021801249340	4021801249357	4021801249364	4021801249371	4021801249388	4021801249395	4021801259134
Color	Black						