

CUBIX™ CROSSLINE LASER

STANLEY

- Self levelling cross line laser
- Single laser diode split with lens
- 3 position power / lock switch
- Integrated slots in housing for quick connection to accessory bracket
- Bracket supplied
- Accurate to 0.8mm/m
- 8m distance laser measuring



NEW



STANLEY	Description	
STHT1-77340	Cubix™ Crossline Laser	Boxed



Product video can be viewed
at www.stanleytools.co.uk

THE PRO'S ADVICE



THE RIGHT LASER TOOL FOR THE JOB

THE MAIN TYPES OF STANLEY LASER TOOLS



Optical Level

Rotary


Cross Line

Spot


THE 4 MAIN FUNCTIONS OF LASER TOOLS



Angles and slopes



Squaring



Plumb line – take a point from floor to ceiling



Horizontal & vertical levelling & alignment

WHAT IS A LASER?

LASER stands for 'Light Amplification by Stimulated Emission of Radiation'. A diode is used to create a concentrated laser beam of light in one wavelength. The shorter the wavelength the brighter and more visible the laser beam. Stanley lasers have a standard wavelength of 635 nanometers, which is suitable for use up to 300m.

IP RATING

When working in dusty and damp conditions, the IP rating of the laser is also important. A selection of Stanley lasers are rated IP54 (dust resistant and splash proof) or IP66 (dust resistant and completely waterproof).

ARE LASERS POTENTIALLY HAZARDOUS?

Lasers are classed from 1 up to 4 in terms of potential hazard. Stanley laser classes range from class I up to class IIM, which pose little or no hazard.

Class I – Poses no threat of biological damage.

Class II – The output could harm a person if they were to stare into a beam for a long period of time.

Class IIM – Lasers have a divergent beam and may be hazardous if an optical instrument is placed in front of the eye such as a magnifying glass.

WARRANTY REPAIR AND CALIBRATION SERVICE

All Stanley laser products are supplied with 1,2,3, or 5 year warranty, against deficiencies in materials and/or workmanship from the date of purchase. We advise that you have your Stanley laser products serviced annually, and calibrated every 6 months. If your product is malfunctioning within or outside the warranty period, you can get in touch with the After Sales Service Agent as listed. Our service agent can arrange collection throughout the country.

Stanley Service Centre
Green Lane, Spennymoor, Co. Durham, DL16 6JG, UK
Helpdesk: (+44) (0) 1753 511234
Email: sicagent@sbdinc.com

**SEE ALL THE PRO'S ADVICE AT
STANLEYTOOLS.CO.UK**