



MULTI-FUNCTION BRUSHER BOX

RC380BC2

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:49





DESCRIPTION

MULTI-FUNCTION BRUSHER BOX

MULTIPURPOSE This brushing machine provides the solution for many paint, mastic and protective coating stripping problems. 'Gum' wheels are very effective for removing adhesives from bodywork without causing any damage. Composite casing. Variable speed control. Ductable rear exhaust. Auxiliary handle. Safety trigger. Supplied with 1 hooked brush 23x105 (ref. 1530-4) and 1 brush holder (ref. 1530-58). Brushing machine for conventional stripping tasks as well as for many stripping problems on difficult surfaces: coatings, mastics etc. Box contents: Brushing machine 1531 or 1531P with 35 mm casing. Brush and gum wheel holder (Ref. 1530-58). 4 hooked brushes 23x105 (Ref. 1530-4). 2 universal brushes 23x105 (Ref. 1530-3). 1 standard gum wheel 30x105 (Ref. 1530-8). 1 soft gum wheel 30x105 (Ref. 1530-9). 1 abrasive wheel holder 15x100 (Ref. 1530-54). 1 abrasive two-wheel holder 15x100 (Ref. 1530-55). 6 abrasive wheels (Ref. 19649N-100). 1 moulded box.

STANDARDS / DIRECTIVES

2006/42/CE, ISO 11148-6, ISO 15744, ISO 28927-2

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:49



SPECIFIC DATA

Designation	MULTI-FUNCTION TANGENTIAL BRUSHER BOX
Sales reference	RC380BC2
Weight (g)	4300
l (mm)	70
L (m)	190
h (mm)	310
Power (W)	550
Rotation speed (rpm)	3 500
Vibration (m/s ²)	2,5
Noise level (dBa)	83
C mm	6,5
C min mm	115
C mm	1/4
Guarantee	M2 SAM Equipment and Machine Guarantee

Guarantee applied

M2 | SAM Equipment and Machine Guarantee

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

>> [Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

