

BIZ5 - Bizweld Work FR Coverall

Collection: Bizweld™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizweld Work: 100% Cotton, 330g

Outer Carton: 12

Product information

The Bizweld FR Coverall offers visible protection to the wearer. Clever design features include flame resistant reflective tape on the shoulders, sleeves and legs, the option to insert knee pads when needed, ample storage space and a rule pocket. A very popular style.

Bizweld™ Work

Bizweld™ Work protective clothing have been specially designed to guarantee comfort, performance and safety whilst providing effective function at all times. Bizweld™ Work has been rigorously tested to ensure total compliance with the latest international standards.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 1 (A1+A2)

IEC 61482-2 IEC 61482-1-1 (ELIM 8.3 CAL/CM², ATPV 10.9 CAL/CM²)

ASTM F1959/F1959M-12 (ATPV 11.2 CAL/CM² (HAF = 80.4%))



Features

- Protection against radiant, convective and contact heat
- Certified protection against molten metal splash
- Two chest pockets with stud closure
- Rule pocket
- Concealed stud front for easy access
- Stud adjustable cuffs for a secure fit
- Available in sizes up to 5XL
- Two tier knee pad pockets allowing two positioning options
- 8 pockets for ample storage
- 40+ UPF rated fabric to block 98% of UV rays
- Radio loops for easy clipping of a radio



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

BIZ5 - Bizweld Work FR Coverall

Commodity Code: 6211321000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

Cert No: 2777 12872 03 E00 00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
BIZ5RBRS	Royal Blue	43.0	28.0	58.0	1.3610	0.0698	5036108167777	25036108731941
BIZ5RBRM	Royal Blue	43.0	28.0	58.0	1.4390	0.0698	5036108167760	25036108609097
BIZ5RBRL	Royal Blue	43.0	28.0	58.0	1.4750	0.0698	5036108167753	25036108609080
BIZ5RBRXL	Royal Blue	43.0	28.0	58.0	1.5990	0.0698	5036108167784	25036108609103
BIZ5RBRXXL	Royal Blue	43.0	28.0	58.0	1.6410	0.0698	5036108167791	25036108609110
BIZ5RBRXXXL	Royal Blue	43.0	28.0	58.0	1.7960	0.0698	5036108167807	25036108688979