

# Potentiometers



Resistive Element    Power (watts)    Resistive Range (ohms)    Tolerance    Resistance Taper (Law)    Body Dimension    Shaft    Bushing    Terminals

## POTENTIOMETERS ■ INDUSTRIAL



Conductive plastic	0.5	150-5 meg	±10%, ±20%	Linear Non-Linear	15/16" dia.	Plain, Slotted Flatted Knurled 1/4" dia. Metal	Plain Locking 3/8" dia. Metal	PC Solder lug Wire-wrap
Conductive plastic	2.0	50-5 meg	±10%, ±20%	Linear Non-Linear	1" dia.	Plain, Slotted Flatted Knurled 1/4" dia. Metal	Plain Locking 3/8" dia. Metal	Solder lug

Note: 53 Series available with rotary switches.

Carbon composition	2.25	50-5 meg	±10, ±20%	Linear Non-Linear	1.156" dia.	Plain, Slotted Flatted 1/4" dia. Metal	Plain Locking Watertight 3/8" dia. Metal	Solder lug
--------------------	------	----------	-----------	----------------------	-------------	---	--	------------

Note: J Series available as Bridged-T, Bridged-H, L and Straight-T attenuators.

Extra long life version of J, with single or dual configurations.								
---	--	--	--	--	--	--	--	--

Conductive plastic	2.0	50-5 meg	±10%, ±20%	Linear Non-Linear	1" dia.	Plain, Slotted Flatted Knurled 1/4" dia. Metal	Plain Locking 3/8" dia. Metal	Solder lug
--------------------	-----	----------	------------	----------------------	---------	--	--	------------

Note: 380 Series available with rotary switches. 100,000 cycle life.

Conductive plastic	1.0	100-5 meg	±10, ±20%	Linear Non-Linear	5/8" dia.	Plain, Slotted Flatted Knurled 1/8" dia. Metal	Plain Locking 1/4" dia. Metal	Solder lug Wire wrap
--------------------	-----	-----------	-----------	----------------------	-----------	--	--	-------------------------

Note: 381 Series available with rotary momentary and alternate action switches.

Conductive plastic	2.0	50-5 meg	±10, ±20%	Linear Non-Linear	1" dia.	Plain, Slotted Flatted Knurled 1/4" dia. Metal	Plain Locking 3/8" dia. Metal	Solder lug
--------------------	-----	----------	-----------	----------------------	---------	--	--	------------

Note: 485 Series has rotational life of +1,000,000 cycles.

# Military

Clarostat provides Mil-spec products including, but not limited to the following units displayed in this catalog:

Industrial	Board Washable	Wirewound	Trimmer	Resistor
Series 53(RV4) Series J(RV4) Series 382(RV6), 392(RV6) G (RV6) and W(RV6)	Series 392 (RV6 & RV8) Series 382(RV6) G (RV6) W(RV6)	Series 43 (RA20) Series 58(RA30)	Series R(RJ11)	Series RW

Consult factory for specific tapers  
Tolerances not included