



Screwdriver socket

54TX



Product no. **03100040**
GTIN **4018754006687**
Model **54 TX T 40**




Label. 1/2 " Screwdriver socket L.55mm

Properties.

- for recessed TORX® screws
- 1/2" internal square drive
- Chrome Alloy Steel, chrome-plated

Technical drawing.



Technical attributes.

Drive profile	TORX®
Internal square drive (inch)	1/2 "
d	22,7 mm
Size of output profile	T40
L1	55 mm
L2	17 mm

Logistics data.

Depth mm (IFS)	55
Width mm (IFS)	23
Height mm (IFS)	23
WEEE/ElektroG	nicht ear-pflichtig
Length (packed, mm)	100
Width (packed, mm)	80

Height (packed, mm)	23
Volume (packed, dm ³)	0.184 dm ³
Art. no.	03100040
Weight (gross, kg)	0,360
Weight PAP (kg)	0,000
Weight PVC (kg)	0,003
GTIN	4018754006687
Country of origin AWR	GERMANY
Region of origin	Nordrhein-Westfalen
Customs tariff no.	82042000
Packing standard	5
Weight	75 g

Variants.

Art. no.	Model no. (ERP)	Description	GTIN
03100020	54 TX T 20	1/2 " Screwdriver socket L.55mm	4018754006649
03100025	54 TX T 25	1/2 " Screwdriver socket L.55mm	4018754006656
03100027	54 TX T 27	1/2 " Screwdriver socket L.55mm	4018754006663
03100030	54 TX T 30	1/2 " Screwdriver socket L.55mm	4018754006670
03100040	54 TX T 40	1/2 " Screwdriver socket L.55mm	4018754006687
03100045	54 TX T 45	1/2 " Screwdriver socket L.55mm	4018754006694
03100050	54 TX T 50	1/2 " Screwdriver socket L.55mm	4018754006700
03100055	54 TX T 55	1/2 " Screwdriver socket L.58mm	4018754006717
03100060	54 TX T 60	1/2 " Screwdriver socket L.58mm	4018754006724
03100070	54 TX T 70	1/2 " Screwdriver socket L.60mm	4018754132362

GTIN.



STAHLWILLE Eduard Wille GmbH & Co. KG

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0 · Fax: +49 202 4791-200
 info@stahlwille.de · www.stahlwille.com · Copyright by STAHLWILLE Eduard Wille GmbH & Co. KG, Wuppertal
 Copyright by STAHLWILLE Eduard Wille GmbH & Co. KG, Wuppertal