



**Part Number :** [191930151](#)

**Product Description :** VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Closed-Brazed Barrel, Stud Size 10 (M5), Mylar Tape Carrier

**Series Number :** 19193

**Status :** Active

**Product Category :** Ring and Spade Terminals

**Engineering Number :** D-350-10T



---

## Documents & Resources

### Drawings

[191930151 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


### Specifications

[PS-19902-015-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Closed-Brazed Barrel, Stud Size 10 (M5), Mylar Tape Carrier
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800753039483

### Agency

CSA	LR18689
UL	E32244

### Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	3.102/g
Packaging Type	Adhesive Tape on Reel
Stud Size	10 (M5)

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	7.19mm max.
Wire Size (AWG)	8
Wire Size mm <sup>2</sup>	8.36

---

## Application Tooling

### Global

Description	Part Number
ATP Crimp Dies for VersaKrimp High Temperature Nickel Plated Steel Terminals on Tape, 8 AWG	<u>190270105</u>
ATP Crimp Dies for VersaKrimp Copper Ring Tongue Terminals And Butt Splices on Tape, 8 AWG	<u>190270111</u>
ATP Crimp Dies for VersaKrimp Ring Tongue Terminals, for Solid Copper or Steel Wire (Anti Rotation)	<u>190270117</u>
ATP Crimp Dies for Versakrimp 8 AWG Ring Tongue Terminals, for Stripped Magnet or Steel 6 AWG Wire	<u>190270120</u>
ATP Perishable Tool Kit used in ATP Presses that Process Product on Tape	<u>190270245</u>
ATP Crimp Dies for VersaKrimp Copper Ring Tongue Terminals and Butt Splices on Tape, 8 AWG, use with Tape Crimp Module and ATP-201 Press	<u>190472000</u>