

TM-RIBBON 110 WH 100 - Ink ribbon



0804661

<https://www.phoenixcontact.com/gb/products/0804661>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon, For THERMOMARK roll printers and THERMOMARK CARD for printing material-off-the-roll product groups: EML ..., EMLP ..., EMLF ..., PML-M ..., WMTB HF-HP..., WMS-2 HF ... RD and US-material product groups: US-EML(S)P ..., US-EMLP-HA ..., US-EM(S)P ..., US-WMT ..., US-WMTB ..., US-PML-M ..., US-EMLF ..., length: 60 m, roll length: 60 m, width: 110 mm, color: white

Commercial data

Item number	0804661
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG1223
Product key	BG1223
Catalog page	Page 35 (C-3-2019)
GTIN	4055626431697
Weight per piece (including packing)	155.1 g
Weight per piece (excluding packing)	6.956 g
Customs tariff number	96121010
Country of origin	DE

TM-RIBBON 110 WH 100 - Ink ribbon



0804661

<https://www.phoenixcontact.com/gb/products/0804661>

Technical data

Product properties

Product type	Ink ribbon
--------------	------------

Marking

Identification technology	Thermal transfer
---------------------------	------------------

Dimensions

Width	110 mm
Length	60 m
Length of roll	60 m

Material specifications

Color	white (RAL 9010)
Material	Polyester

Environmental and real-life conditions

Ambient conditions

Recommended ambient temperature (storage/transport)	5 °C ... 35 °C
Recommended humidity (storage/transport)	30 % ... 80 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	1 Year

TM-RIBBON 110 WH 100 - Ink ribbon



0804661

<https://www.phoenixcontact.com/gb/products/0804661>

Classifications

ECLASS

ECLASS-13.0	19140614
-------------	----------

ETIM

ETIM 9.0	EC001694
----------	----------

UNSPSC

UNSPSC 21.0	44103100
-------------	----------

TM-RIBBON 110 WH 100 - Ink ribbon



0804661

<https://www.phoenixcontact.com/gb/products/0804661>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk