


#### **FEATURES**

- Silver plated copper conductor
- PTFE Insulation to BS3G 210
- Various wire sizes and strands
- Multiple colours, including orange, blue, white and red

# RS PRO PTFE Equipment Wire 0.08 mm<sup>2</sup> CSA, Red 100m

Reel RS Stock No.: 841-7138



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



### **Product Description**

Brought to you by RS PRO, a range of wire and cables which excel within harsh environments. In areas where contamination causes an issue, such as oils, acids or excessive sunlight, these cables are specifically designed to be used within those areas. Highlighted by their copper conductor, these cables are suitable for various applications. All models are highly reliable and excellent quality.

#### **General Specifications**

Туре	A
Wire Style	BS3G210
American Wire Gauge	28
Insulation Material	PTFE
Resistant To	Fuels, Gasoline, Hydraulic Fluid, Lubricants, Oils
Core Strands	7/0.12mm
Conductor Material	Silver Plated Copper
Number of Strands	7
Applications	Construction sites, Car engines, Aeroplanes, Petrol stations

#### **Electrical Specifications**

Voltage Rating	300V
Current Rating	3A
Conductor resistance	244Ω /km



# **Mechanical Specifications**

Cross Sectional Area	0.08mm^2
Sheath Colour	Red
Length	100m
Outer Diameter	0.71mm
Insulation Wall Thickness	0.15mm
Size of Strands	0.12mm
Stranding	7/0.12mm
weight	1.40kg/km

# **Operation Environment Specifications**

Minimum Operating Temperature	-75°C
Maximum Operating Temperature	200°C
Operating Temperature Range	-75°C to 200°C

# **Approvals**

Compliance/Certifications	CSA , RoHS Certificate Of Compliance
Standards Met	BS 3G 210:1996







Product Range:	
RS Code	Description
8417263	PTFE A 19/0.15 black 100m
8417279	PTFE A 19/0.15 white 100m
8417267	PTFE A 19/0.15 pink 100m
8417276	PTFE A 19/0.15 red 100m
8417273	PTFE A 19/0.15 yellow 100m
8417282	PTFE A 19/0.15 blue 100m
8417285	PTFE A 19/0.15 orange 100m
8417291	PTFE A 19/0.15 violet 100m
8417289	PTFE A 19/0.15 green 100m
8417298	PTFE A 19/0.15 brown 100m
8417295	PTFE A 19/0.15 grey 100m

# Harsh Environment Wire

