

Features

- RS PRO and Little Giant dual-branded professional solution
- Non-conductive fibreglass stiles rated up to 30,000V
- Lightweight design for easier transportation and handling
- Integrated Ground Cue® system provides audible and tactile indication when reaching the lowest safe step
- Large standing platform for increased comfort and stability
- Multi-functional integrated tool tray
- Reinforced aluminium treads for durability
- Extra-wide angled feet maximise ground contact
- High-visibility green fibreglass construction
- Suitable for intensive professional use
- Comfortable 75mm deep treads
- Designed to reduce ladder-related injuries

RS PRO by Little Giant®

MightyLite™ GRP Fibreglass Step Ladder



RS PRO® is the own brand of RS. Combining quality, choice and value, RS PRO products are professionally approved and trusted by engineers worldwide. Little Giant® is a registered trademark of Little Giant Ladder Systems.

Product Description

The RS PRO by Little Giant® MightyLite™ Step Ladder is a professional-grade fibreglass step ladder engineered to improve safety, comfort and productivity in demanding work environments. Combining the quality assurance of RS PRO with Little Giant's innovative ladder technology, the MightyLite™ range is designed to help reduce common ladder-related injuries while providing a stable and comfortable working platform.

Manufactured with non-conductive fibreglass stiles and reinforced aluminium treads, the MightyLite™ is ideal for electrical, facilities maintenance and industrial applications. Its lightweight construction, large standing platform and integrated Ground Cue® technology provide users with enhanced confidence and safety when working at height.

Standards and Compliance

Standard	EN131 Professional
Maximum Load Capacity	150kg
Usage Classification	Professional / Intensive Use
Stile Material	GRP Fibreglass
Tread Material	Aluminium

Applications

Electrical installation and maintenance
Facilities management
Construction
Building services
Industrial maintenance
Telecommunications
Utility contractors
HVAC installation
Property maintenance

Technical Specification

Brand	RS PRO by Little Giant®
Product Type	Fibreglass Step Ladder
Material	GRP Fibreglass / Aluminium
Maximum Working Load	150kg
Tread Depth	75mm
Distance Between Treads	300mm
Storage Depth	102mm
Top Platform Size	330 x 330mm
Handrail Height	610mm
Colour	Hi-Visibility Green
Electrical Insulation	Up to 30,000V
Tool Tray	Integrated Multi-Function Tray

Product Dimensions

Stock No.	Treads*	Platform Height (mm)	Approx. Working Height (mm)	Closed Height (mm)	Width (mm)	Weight (kg)
889710	2	565	2515	1291	480	5.5
889711	3	845	2795	1590	518	6.5
889712	4	1130	3080	1890	550	7.2
889713	6	1705	3655	2489	612	10.9

**Includes top platform/tool tray step.*

Open Dimensions

Stock No.	Open Height (mm)	Open Depth (mm)
889710	N/A	705
889711	N/A	896
889712	N/A	1088
889713	2320	1472

Shipping Information

Stock No.	Shipping Length (mm)	Shipping Width (mm)	Shipping Depth (mm)	Gross Weight (kg)
889710	1280	485	370	6.5
889711	1590	530	370	7.7
889712	1890	550	370	9.4
889713	2510	630	370	13.1

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories



Safety Note

Always inspect ladder equipment before use and follow all applicable workplace safety procedures. Ensure the ladder is fully locked into position before climbing.