

molex

Part Number : [2002185900](#)

Product Description : Hand Crimp Tool for Micro-Fit+ Female and Micro-Fit TPA Male Crimp Terminals, 24 AWG, UL1007 and UL1061 Wires

Series Number : 207129

Status : Obsolete

Product Category : Crimp Presses and Crimp Hand Tools



Documents & Resources

Tooling Specifications

[2002185900-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Obsolete
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool for Micro-Fit+ Female and Micro-Fit TPA Male Crimp Terminals, 24 AWG, UL1007 and UL1061 Wires
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	Micro-Fit TPA, Micro-Fit+
Tool Type	Hand Crimp Tool
UPC	191130533664
Warranty Disclaimer	<p>CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where</p>

Molex Tooling is modified.

Applicable Parts

Description	Part Number
Micro-Fit TPA Crimp Terminal, Male, with Tin (Sn) Pre-plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430315003</u>
Micro-Fit TPA Crimp Terminal, Male, with 0.38µm Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430315004</u>
Micro-Fit TPA Crimp Terminal, Male, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430315005</u>
Micro-Fit TPA Crimp Terminal, Male, with 2.54µm Matte Tin Plated Phosphor Bronze Contact, 24-20 AWG, Reel	<u>430315006</u>
Micro-Fit+ Crimp Terminal, Female, Tin (Sn) Plating, 24-20 AWG	<u>2064600021</u>

This document was generated on Sep 23, 2025