



GE
Lighting



ConstantColor™ CMH Single Ended Mini CMH35/TC/UVC/U/830/G8,5 PLUS 1/12 **43273**

Product information

GE's low watt **CMH lamps** have opened new possibilities for lighting design, combining the power and light quality of far larger and less efficient lamps. It is now possible to achieve lighting design that could not be achieved previously with inferior technologies. GE's new **ConstantColor™ CMH Precise™** technology platform has been developed with specific focus to retail applications. GE Precise™ technology offers superb overall light quality, outstanding lumen maintenance, improved efficacy, while maintaining long life and reliability. These qualities are why GE is the leader in ceramic metal halide technology.



WORLDWIDE PARTNER

Product data

Cap/Base	G8.5
Bulb Shape	TC
Bulb Finish	Clear
Maximum Overall Length [mm]	85
Light Center Length [mm]	52
Net weight per piece [g]	9
Gross weight per piece [g]	18
Operating position	U - Universal
Mercury Content [mg]	4.8
UV radiance	Exempt
Brand	General Electric (GE)

Performance data

Colour Code	830
Colour Rendering Index (CRI) [Ra]	84
Nominal correlated colour temperature (CCT) [K]	3000
Nominal lumens [lm]	3400
Rated Lumens [lm]	3520
Nominal efficacy [LpW]	136
Rated efficacy [LpW]	89.2
Energy efficiency class (EEC)	A+
Nominal chromaticity coordinate X	0.435
Nominal chromaticity coordinate Y	0.4
Weighted energy consumption [kWh/1000h]	43.4

Electrical data

Nominal power [W]	35
Rated power [W]	39.5
Nominal lamp voltage [V]	90
Lamp Current [A]	0.4
Design Ambient Temperature [°C]	25
Run-up time (sec)	72
Hot restart time (sec)	420
Dimming Capability	No
Ballast Required	Yes


Logistic data

DUN Code	10043168432730
EAN Code	0043168432733
Pack Quantity	12
Inner pack type	SLEEVE
Outer pack type	OUTER BOX
Layer quantity	960 EUR, 1236 UK
Layer quantity EUR	960
Layer quantity UK	1236
Pallet quantity EUR (PC)	8640
Pallet quantity UK (PC)	11124
Outer case size	138 x 82 x 118 (mm)
Product status	Available


Application areas



Lumen maintenance data



Survival Data



Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[HID Lamps Spectrum Catalogue \(EN\) \(PDF\)](#)

[ConstantColor™ CMH Ultra Brochure \(PDF\)](#)

[ConstantColor™ White Light CMH Brochure \(PDF\)](#)

[ConstantColor™ CMH G8.5 Mini Data sheet \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)