



Foot protection

SAMY3 S7 SR

WATERPROOF

Waterproof high cut shoe thanks to its DELTATEX membrane, dedicated to outdoor environments



Specific benefits



Comfort

- Shock-absorbing heel to relieve joint strain
- Dual-density outsole



Performance

- Waterproof design prevents water penetration
- High stability ensured by the sole's grip properties



Hygiene

- Removable insock for easy cleaning

Certifications and norms



EN ISO 20345

S7 CI HI WR FO A E SR



DELTA-TEX WATERPROOF

Technologies & labels

Applications

- Agriculture
- Public works
- Building
- Finishing works / Craftsmanship
- Events & scenic
- Law enforcement

Protects against risks



Antistatic



Heat



Shock



Cold



enjoy safety.

Edit 10/12/2024
www.deltaplus.eu



Foot protection

SAMY3 S7 SR

WATERPROOF

Waterproof high cut shoe thanks to its DELTATEX membrane, dedicated to outdoor environments

Standards - Details

Technical details

Shoe type	High shoe
Outsole material	PU, 2d
Anti-perforation insert	Stainless steel
Upper material	Leather
Upper finition material	Grain Leather
Safety toe-cap	Stainless steel
Lining material	Membrane, Polyester, Delta-Tex
Lining material finition	Breathable
Footbed material	EVA, Polyester
Footbed caracteristic	Removable, Perforated, Pre-molded
Outsole finition	Injected
Weight (g per shoe)	844
Size range	36 → 48



Safety footwear

SAMY3 S7 SR

WATERPROOF

Waterproof high cut shoe thanks to its DELTATEX membrane, dedicated to outdoor environments

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
SAMY3S7NO39	Black	39	SAMY3 S7 SR	3295249293956	13295249293953	5	1	9.5 kg	28.8 cm	62.8 cm	35.8 cm
SAMY3S7NO40	Black	40	SAMY3 S7 SR	3295249293963	13295249293960	5	1	9.5 kg	28.4 cm	62.4 cm	35.4 cm
SAMY3S7NO41	Black	41	SAMY3 S7 SR	3295249293970	13295249293977	5	1	9.9 kg	28.2 cm	62.2 cm	36.2 cm
SAMY3S7NO42	Black	42	SAMY3 S7 SR	3295249293987	13295249293984	5	1	10.1 kg	28.4 cm	62.2 cm	35.4 cm
SAMY3S7NO43	Black	43	SAMY3 S7 SR	3295249293994	13295249293991	5	1	10.3 kg	39.0 cm	67.0 cm	30.2 cm
SAMY3S7NO44	Black	44	SAMY3 S7 SR	3295249294007	13295249294004	5	1	10.7 kg	38.8 cm	68.2 cm	29.4 cm
SAMY3S7NO45	Black	45	SAMY3 S7 SR	3295249294014	13295249294011	5	1	11.2 kg	39.2 cm	67.4 cm	29.6 cm
SAMY3S7NO46	Black	46	SAMY3 S7 SR	3295249294021	13295249294028	5	1	11.4 kg	39.0 cm	67.6 cm	29.8 cm
SAMY3S7NO47	Black	47	SAMY3 S7 SR	3295249294038	13295249294035	5	1	11.6 kg	39.0 cm	67.0 cm	30.0 cm
SAMY3S7NO48	Black	48	SAMY3 S7 SR	3295249294045	13295249294042	5	1	12.7 kg	38.4 cm	31.2 cm	67.2 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height