

DCS355NT-XJ

Multi-cutter XR 18V Brushless - 32 accessoires



5035048555491

Product Description:

Variable speed (osc/min) : 0-20000Tool-Free (°) : 1.6Change
Accessory Angle



Product features and benefits:

- Bright LED light illuminates dark work surfaces for precise cutting
Accessory quick change system allows blades and other accessories to be changed quickly without wobbling
- need tools Brushless motor provides up to 57% more run time
- compared to a brushed motor 35-piece accessory set to support an assortment of cutting and sandblasting applications Universal adapter
- for use with most brands of oscillating tool accessories
-
- Robust TSTAK II case included Variable speed trigger allows for the right speed and full control of the application to be performed 3-position pendulum movement for greater efficiency
-

Specifications techniques :

- Voltage: 18 V
- Output power: 300 W

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Wood blade with nails 31 x 43 mm
- (x1) Fast-cutting wood blade 31 x 43 mm
- (x1) Sanding pad (x1) TSTAK set (x1)
- Universal adapter (x1) Assorted sanding sheets (x25)
-
-

DCS355NT-XJ

Multi-cutter XR 18V Brushless - 32 accessoires

5035048555491



Product in the composition DCS355NT-XJ

Ref	Title
330019-03	SCREW
330045-43	SCREW
605040-02	BEARING
90583886	EXTERNAL FLANGE
90583887	SCREW
90583888	RING
N129813-03	BEARING, BALL
N140357	SPRING
N140388	TRUNK
N140406	BEARING
N146419	PLATE
N146423	CLIP
N150641	O-RING
N163918	LOCK BUTTON
N165498	SPRING
N175484	SCREW
N184706	OFF
N233819	DEL
N238819	BUMPER
N241039	RUBBER PAD
N243985	NUT
N251926	BLADE
N251931	BLADE - RIGID SCRAPER
N254620	S/E COLLIER
N266442	RUBBER PAD

Ref	Title
N271240	PLATEAU
N275341	DEPTH GAUGE
N275350	S/E BLOCK
N277679	FOAM
N278060	FOAM
N278801	S/ENS BUTTON
N291362	SCREW
N306040	LABEL BRAND
N306579	ETIQUETTE
N328739	RUBBER PAD
N328740	RUBBER PAD
N328741	RUBBER PAD
N342939	BLADE - CARBIDE
N376932	OUTER COLLAR
N409476	LOCK
N409477	LATCH
N440293	BRIDLE
N615986	KIT BOX
N615998	HANDLE
N697388	TRIGGER
N728006	BUMPER
N728008	BUMPER
N762313	SHELL SET
N771496	INSERT
NA105864	NAMEPLATE
NA126544	ETIQUETTE