

1324135

<https://www.phoenixcontact.com/in/products/1324135>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Replacement die for CRIMPFOX-TC HC 10, CK 4,0-ED... turned contacts, 2 marked die stations



Your advantages

- Marked die stations for precise processing of corresponding cross sections

Commercial data

Item number	1324135
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	BH313Y
GTIN	4063151610487
Weight per piece (including packing)	50.88 g
Weight per piece (excluding packing)	50.88 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX-TC HC 10/DIE - Replacement die



1324135

<https://www.phoenixcontact.com/in/products/1324135>

Technical data

Notes

Note on application	For 6.0 mm ² ... 10.0 mm ² turned crimp contacts from the CK4.0 ED... series, the packing slip includes a detailed list of the crimp contacts
---------------------	---

Product properties

Product type	Die
Compression	Square crimp

Crimping position 1

Max. cross section	6 mm ²
AWG max	10

Crimping position 2

Max. cross section	10 mm ²
AWG max	8

Connection data

Conductor connection

Cross section range, metric	6 mm ² ... 10 mm ²
Cross section range AWG	10 ... 8

Material specifications

Color	black (RAL 9005)
Material	Steel

CRIMPFOX-TC HC 10/DIE - Replacement die



1324135

<https://www.phoenixcontact.com/in/products/1324135>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1324135>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-TC HC 10/DIE - Replacement die



1324135

<https://www.phoenixcontact.com/in/products/1324135>

Classifications

ECLASS

ECLASS-11.0	21043852
ECLASS-12.0	21043852
ECLASS-13.0	21043852

ETIM

ETIM 9.0	EC001282
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-TC HC 10/DIE - Replacement die



1324135

<https://www.phoenixcontact.com/in/products/1324135>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

CRIMPFOX-TC HC 10/DIE - Replacement die



1324135

<https://www.phoenixcontact.com/in/products/1324135>

Accessories

CK4,0-ED-10,00M AG - Crimp contact

1274091

<https://www.phoenixcontact.com/in/products/1274091>



Crimp contact, contact diameter: 4 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 10 mm² ... 10 mm², AWG 8

CK4,0-ED-10,00F AG - Crimp contact

1274085

<https://www.phoenixcontact.com/in/products/1274085>



Crimp contact, contact diameter: 4 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 10 mm² ... 10 mm², AWG 8

CRIMPFOX-TC HC 10/DIE - Replacement die



1324135

<https://www.phoenixcontact.com/in/products/1324135>

CK4,0-ED-6,00M AG - Crimp contact

1274092

<https://www.phoenixcontact.com/in/products/1274092>



Crimp contact, contact diameter: 4 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 6 mm² .. 6 mm², AWG 10

CK4,0-ED-6,00F AG - Crimp contact

1274086

<https://www.phoenixcontact.com/in/products/1274086>



Crimp contact, contact diameter: 4 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 6 mm² .. 6 mm², AWG 10

CRIMPFOX-TC HC 10/DIE - Replacement die

1324135

<https://www.phoenixcontact.com/in/products/1324135>



UNIFOX RT-CK 4.0 - Contact removal tool

1072064

<https://www.phoenixcontact.com/in/products/1072064>

Contact removal tool, for rotated CK-4,0-... contacts



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in