

## Fuse Kit Surface Mount Fuse UMF 250 / UMK 250



### Description

- Fuse Kit for quick sampling of customers and engineering design support
- More technical data and approvals see the specific datasheets

### References

Fuse Kit to [UMF 250](#); [UMK 250](#)

### Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

### Fuse Kit UMF 250 / UMK 250

Type	Rated current	Rated Voltage [VAC]	Rated Voltage [VDC]	Amount	Part Number
UMF 250	500 mA	250	125	10 pieces	<a href="#">3405.0163.11</a>
UMF 250	630 mA	250	125	10 pieces	<a href="#">3405.0164.11</a>
UMF 250	800 mA	250	125	10 pieces	<a href="#">3405.0165.11</a>
UMF 250	1 A	250	125	10 pieces	<a href="#">3405.0166.11</a>
UMF 250	1.25 A	250	125	10 pieces	<a href="#">3405.0167.11</a>
UMF 250	1.6 A	250	125	10 pieces	<a href="#">3405.0168.11</a>
UMF 250	2 A	250	125	10 pieces	<a href="#">3405.0169.11</a>
UMF 250	2.5 A	250	125	10 pieces	<a href="#">3405.0170.11</a>
UMF 250	3.15 A	250	125	10 pieces	<a href="#">3405.0171.11</a>
UMF 250	4 A	250	125	10 pieces	<a href="#">3405.0172.11</a>
UMF 250	5 A	250	125	10 pieces	<a href="#">3405.0173.11</a>
UMF 250	6.3 A	250	125	10 pieces	<a href="#">3405.0174.11</a>
UMF 250	8 A	250	125	10 pieces	<a href="#">3405.0175.11</a>
UMF 250	10 A	250	125	10 pieces	<a href="#">3405.0176.11</a>
UMK 250	500 mA	250	125	10 pieces	<a href="#">3404.2463.11</a>
UMK 250	1 A	250	125	10 pieces	<a href="#">3404.2466.11</a>
UMK 250	2 A	250	125	10 pieces	<a href="#">3404.2469.11</a>
UMK 250	4 A	250	125	10 pieces	<a href="#">3404.2472.11</a>

### Variants kit

Description	Order Number
Fuse Kit UMF 250/UMK 250	<a href="#">3405.0199</a>

**Packaging Unit** 1 Pcs