


535432 CLR-12-10-L-P-A Linear/swivel clamp - Series: All



535432 CLR-12-10-L-P-A Linear/swivel clamp - Series: All

Pos.	Part no.	Type	Note	Qty.	Unit
A	673615	CLR-12-...-P-A Set of wearing parts	Spare parts: 5, 9, 12, 14, 20, 24, 25	1	PC
1	207727	ISO 4762-M3X10-8.8 Socket head screw	Tightening torque 1.5	1	PC
2		CLR-12/16 Clamping finger	Not available separately, see position 6	1	PC
3	200715	DIN 934-M4-6AU Hex nut	Tightening torque 0.5	1	PC
4	672297	M4X25 Hexagon head screw		1	PC
5	671069	8.2X11X6.5 Cover cap		1	PC
6	535551	CLR-12-FS Clamping arm		1	PC
7	658854	ADN-12/16 flange screw	Use locking compound. See position 25 Tightening torque 7.5 Nm/ 5.5 lbf ft	4	PC
8		CLR-12 Bearing cap	Not available separately, see position 11	1	PC
9	369850	WIFC1-6X9X2,8-TPE-U Wiper seal	Grease using during assembly. See position 24	1	PC
10		CLR-12 Bearing	Not available separately, see position 11	1	PC
11	669808	CLR-12 Bearing cap module		1	PC
12		B-12X1-N-NBR75 O-ring ISO3601	Grease using during assembly. See position 24 Not available separately, see position A	2	PC
13		IRA-06-S0045,1-IK Piston rod	Not available	1	PC
14		BA-K10D-012-A Complete piston	Grease using during assembly. See position 24 Not available separately, see position A	1	PC
15		CLR-12-10 Guide sleeve	Not available separately, see position 18 Grease using during assembly. See position 24	1	PC
16		DIN 7344-2X10 Spring pin	Not available separately, see position 18	1	PC
17	669891	CLR-12-10 Guide rod	When ordering please specify the stroke (see type plate) Tightening torque 1.5 Nm/ 1.1 lbf ft	1	PC
18	677721	CLR-12-10 Piston rod module		1	PC
19		CLR-12-10 Cylinder barrel	Not available	1	PC
20		B-4,5X1-N-NBR70 O-ring ISO3601	Not available separately, see position 22+999 Grease using during assembly. See position 24	1	PC
21		CLR-12 Guide pin	Not available separately, see position 22 Use locking compound. See position 25	1	PC
22	669839	CLR-12 Pin module	Tightening torque 3 Nm/ 2.2 lbf ft	1	PC
23		CLR-12 End cap	Not available	1	PC
24	684474	LUB-KC1 SILIKONFREI 20ML Lubricating grease		1	PC
25	8181256	CYBERBOND TM44 TB1ML Adhesive bonding agent		1	PC