



Part Number : [2257755622](#)

Product Description : Pre-Crimped Lead HFM Jack
Terminal-to-HFM Plug Terminal Off-the-Shelf (OTS)
Cable Assembly, RG-174 Cable, 1000.00mm Length, 50
Ohms

Series Number : 225775

Status : Active

Product Category : RF Cable Assemblies



Documents and Resources

Drawings

[2257755622 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2079110012-000.pdf](#)

[2088700000PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF Cable Assemblies
Series	225775
Description	Pre-Crimped Lead HFM Jack Terminal-to-HFM Plug Terminal Off-the-Shelf (OTS) Cable Assembly, RG-174 Cable, 1000.00mm Length, 50 Ohms
Application	Automotive, RF, Wire-to-Wire, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	HFM Terminal-to-HFM Terminal
Product Name	High-Speed FAKRA Mini (HFM)
Type	RF Cable Assembly
UPC	198930326663

Electrical

Impedance	50Ω
-----------	-----

Physical

Cable Length	1000.00mm
Gender	Jack Terminal/Plug Terminal
Material - Metal	Spring Bronze
Material - Plating Mating	Gold

Material - Resin	N/A
Net Weight	19.459/g
Packaging Type	Carton
Single Ended	No
Wire/Cable Type	RTK031

Mates With / Use With

Use with Part(s)

Description	Part Number
High-Speed FAKRA Mini (HFM) Jack Housings and Terminals	<u>207911</u>
High-Speed FAKRA Mini (HFM) Plug Housings and Terminals	<u>207912</u>