



Cold



Medium Duty

Cold weather work gloves offering reliable grip, abrasion and cold protection

- **Heightened defenses:** Tested to perform at -4°F/-20°C, ActivArm® 97-011 cold weather gloves' two-ply acrylic brushed liner ensures effective hand protection against the elements, as well as oil and abrasion
- **Optimized comfort and dexterity:** These breathable work gloves are also great for maintaining all-day comfort, delivering heightened dexterity and limiting hand fatigue, and are ideal for prolonged use
- **Tightened grip:** ActivArm® 97-011 industrial gloves feature a double-dipped sandy nitrile coating, which ensures a secure hold not only in the coldest weather, but also in wet and oily conditions, protecting hands by keeping them warm and dry
- **Enhanced features:** These hand protection gloves are characterized by their contrasting black coating and orange liner combination, which guarantees better visibility and safety in high-risk, low-light situations



Industries

- Chemical
- Construction

Applications

- Loading trucks & vehicles
- Product shipping, transport and delivery
- Cold Storage
- Construction
- Maintenance

Key Features

- **Two-ply acrylic brushed liner:** Cold and abrasion resistance
- **Three-quarter, double-dipped nitrile coating with sandy finish:** Superb grip
- **Orange liner:** For truly effective, increased visibility safety gloves

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® 97-011	Finishing: ¾ Coated Coating Material: Nitrile Liner Material: Acrylic, Polyester Cuff Style: Knitwrist	10	8, 9, 10, 11	240-275 mm; 9.64-10.82	Black	6 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
 Riverside Business Park
 Blvd International, 55
 1070 Brussels, Belgium
 T: +32 (0) 2 528 74 00
 F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
 Blvd. Bernardo Quintana No. 7001-C,
 Q7001 Torre II,
 Suites 1304, 1305 y 1306,
 Col. Centro Sur, c.p. 76079
 Queretaro, Qro. Mexico
 T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
 111 Wood Avenue South,
 Suite 900
 Iselin, NJ 08830, USA
 T: +1 800 800 0444
 F: +1 800 800 0445

Canada

Ansell Canada
 105 Lauder
 Cowansville, QC J2K 2K8
 Canada
 T: +1 800 363 8340
 F: +1 800 267 3551

Australia

Ansell Limited
 Level 3, 678 Victoria Street,
 Richmond, Vic, 3121
 Australia
 T: +61 1800 337 041
 F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
 (Malaysia) Sdn Bhd
 Prima 6, Prima Avenue
 Block 3512, Jalan Teknokrat 6
 T: +603 8310 6688
 F: +603 8310 6699