

## Screwdriver socket

**54TX**



Product no. **03100030**  
GTIN **4018754006670**  
Model **54TX T30 TORX®**




**Label.** 1/2 " Screwdriver socket L.55mm

**Properties.**

- for recessed TORX® screws
- 1/2" internal square drive
- Chrome Alloy Steel, chrome-plated

## Technical drawing.



## Technical attributes.

Drive profile	TORX®
Square drive inner (inch)	1/2 "
d	22,7 mm
Size drive profile	T30
L1	55 mm
L2	17 mm

## Logistics data.

Depth mm (IFS)	55
Width mm (IFS)	23
Height mm (IFS)	23
WEEE/ElektroG	nicht ear-pflichtig
Length (packaged, mm)	100
Width (packaged, mm)	80

Height (packaging, mm)	23
Volume (packaged, dm <sup>3</sup> )	0.184 dm <sup>3</sup>
Product no.	03100030
Weight (gross, kg)	0,360
Weight PAP (kg)	0,000
Weight PVC (kg)	0,003
GTIN	4018754006670
Country of origin AWR	GERMANY
Region of origin	Nordrhein-Westfalen
Customs tariff no.	82042000
Packing standard	5
Weight (g)	72 g

## Variants.

Product no.	Model No. (ERP)	Description	GTIN
03100020	54TX T20 TORX®	1/2 " Screwdriver socket L.55mm	4018754006649
03100025	54TX T25 TORX®	1/2 " Screwdriver socket L.55mm	4018754006656
03100027	54TX T27 TORX®	1/2 " Screwdriver socket L.55mm	4018754006663
03100030	54TX T30 TORX®	1/2 " Screwdriver socket L.55mm	4018754006670
03100040	54TX T40 TORX®	1/2 " Screwdriver socket L.55mm	4018754006687
03100045	54TX T45 TORX®	1/2 " Screwdriver socket L.55mm	4018754006694
03100050	54TX T50 TORX®	1/2 " Screwdriver socket L.55mm	4018754006700
03100055	54TX T55 TORX®	1/2 " Screwdriver socket L.58mm	4018754006717
03100060	54TX T60 TORX®	1/2 " Screwdriver socket L.58mm	4018754006724
03100070	54TX T70 TORX®	1/2 " Screwdriver socket L.60mm	4018754132362

## GTIN.



**STAHLWILLE Eduard Wille GmbH**

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH, Wuppertal