

Features

- Engineered for precise straight cuts in very thin, non-perforated metal sheets.
- Made from fully hardened, high-grade High-Speed Steel (HSS), it features a very fine 0.7mm tooth pitch, ideal for cutting metal thicknesses from 0.5 to 1.5mm.

Jigsaw Blade –Metal T118G –Standard Cut

RS Stock No.: 0757838



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Jigsaw Blade

0757838 Standard for Metal Jigsaw Blade is engineered for precise straight cuts in very thin, non-perforated metal sheets. Made from fully hardened, high-grade High-Speed Steel (HSS), it features a very fine 0.7mm tooth pitch, ideal for cutting metal thicknesses from 0.5 to 1.5mm. Perfect for delicate metalworking tasks requiring accuracy and a clean finish.

- *Wavy Set Teeth for fine, straight cutting*
- *Suitable for use on Mild Steel, Sheet Steel, High Grade Steel & Steel Pipes*
- *Bayonet (T-Shank) fitting system compatible with all popular brands of bayonet fitting machines*
- *Supplied in 5pc Packs*

General Specifications

Tooth Design	Wavy Set, Milled
Type	Jigsaw Blade
Teeth Spacing	0.7mm
Cut Depth	0.5-1.5mm
Cut Type	Standard Cutting
Material	High Speed Steel
Fitting	Bayonet (T-Shank)
Length	77mm

Stock No.	Cut Type	Teeth Spacing	Length	Tooth Design
XXX-XXXX 0757836	Standard Cutting	1.1-1.5mm	77mm	Wavy Set, Milled
XXX-XXXX 0757837	Standard Cutting	1.9-2.3mm	77mm	Wavy Set, Milled
XXX-XXXX 0757838	Standard Cutting	0.7mm	77mm	Wavy Set, Milled
XXX-XXXX 0757839	Standard Cutting	1.2mm	132mm	Wavy Set, Milled
XXX-XXXX 0757840	Standard Cutting	2.0mm	132mm	Wavy Set, Milled
XXX-XXXX 0757842	Special Cutting	3.0mm	100mm	Side Set, Milled

Approvals

Declarations	REACH DoC
---------------------	-----------

Similar Products

Stock No.	Brand	Product Name	Cut Type	Teeth Spacing	Length	Tooth Design
XXX-XXXX 0757836	RS PRO	Jigsaw Blade	Standard Cutting	1.1-1.5mm	77mm	Wavy Set, Milled
XXX-XXXX 0757837	RS PRO	Jigsaw Blade	Standard Cutting	1.9-2.3mm	77mm	Wavy Set, Milled
XXX-XXXX 0757838	RS PRO	Jigsaw Blade	Standard Cutting	0.7mm	77mm	Wavy Set, Milled
XXX-XXXX 0757839	RS PRO	Jigsaw Blade	Standard Cutting	1.2mm	132mm	Wavy Set, Milled
XXX-XXXX 0757840	RS PRO	Jigsaw Blade	Standard Cutting	2.0mm	132mm	Wavy Set, Milled
XXX-XXXX 0757842	RS PRO	Jigsaw Blade	Special Cutting	3.0mm	100mm	Side Set, Milled

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories