



**Torqwrench 1/2" insulated 1000V
capacity 20-100Nm**

Z-854-S

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:15:11





DESCRIPTION



Torqwrench 1/2" insulated 1000V capacity 20-100Nm

Adjusted torque locking system.

Double scale Nm/lbf-ft

USE

Tools for precision tightening of right-hand threads by tripping.

Easy tightening torque adjustment by screwing the wide handle in or out.

When the torque is reached, the handle trips, with an audible and touch detectable signal. The tool rearms automatically.

After use, set the cursor to the minimum torque value. An annual calibration check is recommended within the framework of normal use (possible at the factory).

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:15:11



Advice: do not use for loosening

CHARACTERISTICS

Tool type II - class A - precision +/-3% of the value displayed.

Double scale Nm and lbf.ft. Resolution: 1 Nm.

72-tooth mechanism for 5° angle ratcheting.

Automatic tripping and rearming.

Adjusted torque locking system.

Enables tightening of right-hand threads.

Tool identified by a serial number, supplied with an ISO6789 calibration certificate.

STANDARDS / DIRECTIVES

CEI 60900, NF ISO 6789-1, NF EN 60900

SPECIFIC DATA

Designation	TORQWRENCH 1/2 INSULATED 1000V CAPACITY 20-100NM
Sales reference	Z-854-S
L (mm)	450
Weight (g)	1350
H (mm)	89
d1 (mm)	50
square	1/2"
Capacity (Nm)	30 - 150
Ft.lb	14,75 - 73,75
Guarantee	M1 SAM Equipment and Machine Guarantee:

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>



Guarantee applied

M1 | SAM Equipment and Machine Guarantee:

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:15:11

