

PRODUCT-DETAILS

TAC-W7-G5-RD-MC-0

TAC-W7-G5-RD-MC-0 Terra AC wallbox type 2, cable 5m, 1-phase/32A, MID certified, with RFID, display and 4G



General Information

Extended Product Type	TAC-W7-G5-RD-MC-0
Product ID	6AGC085386
EAN	8719874451628
Alternative Product Reference	3Q510003300A
Catalog Description	TAC-W7-G5-RD-MC-0 Terra AC wallbox type 2, cable 5m, 1-phase/32A, MID certified, with RFID, display and 4G
Long Description	TAC-W7-G5-RD-MC-0 Terra AC wallbox type 2, cable 5m, 1-phase/32A, MID certified, with RFID, display and 4G

Technical

EV Connectors	(AC Type 2) 1 piece
Number of Socket Outlets	AC Type 2 cable only
Cable Length	5 m
Output Power	Nominal 7 kW
Output Voltage (U _{out})	AC 1-phase 184 ... 276 V
Output Current	1-phase 32 A
Connection Power	Nominal 7 kW
Supply Voltage	AC 1-phase 184 ... 276 V
Input Current	1-phase 32 A
Operating Frequency (f _{sw})	50 ... 60 Hz
Number of Phases	1
Connection	TT, TN

Configuration

Number of RCDs Electric Vehicle Supply Equipment	Resid. Curr. Monitor
Number of Miniature Circuit Breakers (MCBs)	0
Overvoltage Category	III
Overload Protection	Overcurrent protection at 40 A
Ambient Air Temperature	Operation -30 ... +50 °C Storage -50 ... +80 °C
Maximum Operating Altitude Permissible	2000 m
Communication Interface	Wi-Fi Ethernet Bluetooth Modbus 4G
Load Management Method	OCP - Based
Authentication Method	RFID App Free Vending
Energy Meter Type	AC-MID
Screen Size	3.5 in
Mounting Type	Wall mounting
Housing Material	Plastic
Degree of Protection	acc. to IEC 60529 IP54
Impact Resistance Rating	IK08

Dimensions

Product Net Length	450 mm
Product Net Depth / Length	0.125 m
Product Net Height	350 mm
Product Net Weight	6 kg
Package Level 1 Units	pallet (lift) 18 piece
Package Level 1 Width	960 mm
Package Level 1 Height	1090 mm
Package Level 1 Depth / Length	1120 mm
Package Level 1 Gross Weight	130 kg
Package Level 1 EAN	8719874451628
Package Level 2 Units	box 18 piece
Package Level 2 Width	0.96 m
Package Level 2 Height	1.206 m
Package Level 2 Depth / Length	1.12 m
Package Level 2 Gross Weight	128 kg

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85371091
Selling Unit of Measure	piece
Minimum Order Quantity	6 piece
EAN	8719874451628
ETIM 8	EC002883 - Charging device E-Mobility

UNSPSC

25175002

IDEA Granular Category Code (IGCC)

1311 >> Electric vehicle charging station

Additional Information

Declaration of Conformity - CE

9AKK107991A0511

RoHS Status

Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

WEEE Category

5. Small Equipment (No External Dimension More Than 50 cm)

Standards

EN 61851-1, EN 61851-23, EN 61000-6-2, EN 61000-6-3, EN 301 908-2, IEC 60721-3-2: IE23, RoHS

Categories

Electric Vehicle Charging → AC Charging Wallbox → AC Chargers type 2

