
Features

- Grade 10 connecting link for assembling chain slings
- Available from 6mm to 32mm lifting chains
- Available from 1.4t to 40T Working Load Limit
- Automatically closes and lockes when lifted
- Luminous red powder painted finish

RS PRO Self Locking Hook, With Eye



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Self-Locking Hook, with Eye

The RS PRO Self-Locking Hook with Eye is a Grade 10 lifting chain component designed for safe and secure use in chain sling assemblies. The hook automatically closes and locks when a load is lifted, helping to reduce the risk of accidental release during lifting operations.

The hook can be opened by pressing the pawl on the back of the hook, while the non-removable latch provides added safety and helps prevent incorrect removal or tampering during use. The eye connection allows the hook to be fitted to compatible chain sling assemblies using a suitable connecting link.

Available for **6mm to 32mm chain sizes**, with working load limits from **1.4t to 40t**, this hook is suitable for a wide range of lifting applications. It is manufactured from high-strength **Grade 10 alloy steel** and finished in luminous red powder paint for durability and easy identification.

Each component is type tested and fatigue rated to **20,000 cycles at 1.5 times the WLL**, with full traceability through batch marking. It meets **EN 1677-3 +25% WLL** and **AS 3776**, with a safety factor of **4:1**.

The component may also be used with Grade 8 chain to **EN 818-2**, provided the complete chain sling is rated as Grade 8 in accordance with **EN 818-4**.

General Specifications

Product Type	Lifting Hooks
Sub Type	Self locking hook with eye
Material	Grade 10 Alloy steel
Working Load Limit	See details below
Weight	See details below
Standards/Approvals	EN1677

Stock No.	Product Name	Working Load Limit	Weight kg
904910	Self Locking Hook w/ Eye	1.4	0.5
904911	Self Locking Hook w/ Eye	2.5	0.9
904903	Self Locking Hook w/ Eye	4	1.5
904904	Self Locking Hook w/ Eye	6.7	2.7
904905	Self Locking Hook w/ Eye	10	5.7
904906	Self Locking Hook w/ Eye	16	7.9
904907	Self Locking Hook w/ Eye	19	11.2
904908	Self Locking Hook w/ Eye	26.5	20.5
904909	Self Locking Hook w/ Eye	40	40.4

Approvals

Declarations	2.2 Certificate
Standards Met	EN1677

Similar Products

Stock No.	Brand	Product Name	Product Type	Working Load Limit	Weight (kg)
904899	RS PRO	Lifting Hook	Container	16t	4
904900	RS PRO	Lifting Hook	Container	16t	4
904901	RS PRO	Lifting Hook	Container	16t	4
904897	RS PRO	Lifting Hook	Connecting Link	1.4t	0.08
904898	RS PRO	Lifting Hook	Connecting Link	2.5t	0.18
904888	RS PRO	Lifting Hook	Connecting Link	4t	0.34
904890	RS PRO	Lifting Hook	Connecting Link	6.7t	0.68
904891	RS PRO	Lifting Hook	Connecting Link	10t	1.22
904892	RS PRO	Lifting Hook	Connecting Link	16t	2.13
904893	RS PRO	Lifting Hook	Connecting Link	19t	3
904894	RS PRO	Lifting Hook	Connecting Link	26.5	5.22
904896	RS PRO	Lifting Hook	Connecting Link	40	9.55
904910	RS PRO	Lifting Hook	Self-Lock w/ Eye	1.4	0.5
904911	RS PRO	Lifting Hook	Self-Lock w/ Eye	2.5	0.9
904903	RS PRO	Lifting Hook	Self-Lock w/ Eye	4	1.5
904904	RS PRO	Lifting Hook	Self-Lock w/ Eye	6.7	2.7
904905	RS PRO	Lifting Hook	Self-Lock w/ Eye	10	5.7
904906	RS PRO	Lifting Hook	Self-Lock w/ Eye	16	7.9
904907	RS PRO	Lifting Hook	Self-Lock w/ Eye	19	11.2
904908	RS PRO	Lifting Hook	Self-Lock w/ Eye	26.5	20.5
904909	RS PRO	Lifting Hook	Self-Lock w/ Eye	40	40.4
904879	RS PRO	Lifting Hook	Sling Hook	1t	0.7
Stock No.	**Brand**	**Product Name**	**Product Type**	**Working Load Limit**	**Weight (kg)**
904880	RS PRO	Lifting Hook	Sling Hook	2t	1.3

904881	RS PRO	Lifting Hook	Sling Hook	3t	2.3
904882	RS PRO	Lifting Hook	Sling Hook	5t	4.6
904886	RS PRO	Lifting Hook	Sling Hook with Swivel	1.4	0.65
904887	RS PRO	Lifting Hook	Sling Hook with Swivel	2.5	0.95
904883	RS PRO	Lifting Hook	Sling Hook with Swivel	4	1.7
904884	RS PRO	Lifting Hook	Sling Hook with Swivel	6.7	3.1
904885	RS PRO	Lifting Hook	Sling Hook with Swivel	10	5.4
904877	RS PRO	Lifting Hook	Sling Hook with Eye	1.4t	0.27
904878	RS PRO	Lifting Hook	Sling Hook with Eye	2.5t	0.65
904912	RS PRO	Lifting Hook	Sling Hook with Eye	4t	1.22
904913	RS PRO	Lifting Hook	Sling Hook with Eye	6.7t	2.43
904871	RS PRO	Lifting Hook	Sling Hook with Eye	10t	3.81
904872	RS PRO	Lifting Hook	Sling Hook with Eye	16t	6.2
904874	RS PRO	Lifting Hook	Sling Hook with Eye	19t	11.5
904875	RS PRO	Lifting Hook	Sling Hook with Eye	26.5t	12.2
904876	RS PRO	Lifting Hook	Sling Hook with Eye	40t	17.5