

### Features

- Designed to be used with aluminium or steel square tube box section
- Glass reinforced nylon and stainless-steel construction
- Push-fit the threaded bush into the square box section

### **RS PRO Threaded Bush, 50mm Width, Nylon, Stainless Steel Insert, M16, For 2mm Wall Thickness Tube**

RS Stock No.: 0285741



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Threaded bushes are designed to be used with aluminium or steel square box section tubing. These tough glass reinforced nylon inserts allow convenient and secure fitment of levelling mounts to various types of equipment. The bush is pressed into the square tubing and remains secure via the compression of the moulding within the tubing.


These tube inserts are suitable for use on catering equipment, spa & hot tubs, conveyor lines and much more

## General Specifications

|                    |                                                                                                                                     |
|--------------------|-------------------------------------------------------------------------------------------------------------------------------------|
| <b>Width</b>       | 50mm                                                                                                                                |
| <b>Material</b>    | Glass reinforced nylon                                                                                                              |
| <b>Thread size</b> | M16                                                                                                                                 |
| <b>Colour</b>      | Black                                                                                                                               |
| <b>Application</b> | Various types of furniture, processing and packaging machinery and equipment, catering equipment, spa and hot tubs, conveyor lines. |

## Mechanical Specifications

|                       |      |
|-----------------------|------|
| A                     | 50   |
| B                     | 44   |
| C                     | 46.5 |
| Thread size           | M16  |
| To fit wall thickness | 2    |



## Similar Products

| Stock No. | Brand  | Product Name  | Width | Thread Size |
|-----------|--------|---------------|-------|-------------|
| 0285736   | RS PRO | Threaded Bush | 30mm  | M10         |
| 0285738   | RS PRO | Threaded Bush | 40mm  | M10         |
| 0285739   | RS PRO | Threaded Bush | 40mm  | M16         |
| 0285741   | RS PRO | Threaded Bush | 50mm  | M16         |
| 0285742   | RS PRO | Threaded Bush | 50mm  | M16         |
| 0285744   | RS PRO | Threaded Bush | 40mm  | M12         |
| 0285745   | RS PRO | Threaded Bush | 30mm  | M12         |
| 0285746   | RS PRO | Threaded Bush | 40mm  | M12         |
| 0285748   | RS PRO | Threaded Bush | 40mm  | M16         |
| 0285749   | RS PRO | Threaded Bush | 50mm  | M20         |