

- Designed for fast and efficient cutting of aluminium & copper wires and plastic sheathed cables
- Stainless steel razor sharp shearing blades for outstanding cutting performance
- Spring assisted blade opening with safety closing catch for convenience
- PVC coated handles for comfort and grip



### Cable snips

Item Number	Length	Quantity
430008	165mm 6 1/2"	3

- Heavy duty design for shearing soft cables, insulation materials, tape, cable ties and many other materials
- Micro serrated stainless steel blades, hollow ground for self sharpening, superior cutting performance
- Integrated cutting notch for effective cable & wire stripping
- Belt pouch for convenient storage



### Electrician's scissors

Item Number	Length	Quantity
492001	140mm 10"	6

## CABLE TIE GUNS

- Designed for automatic tensioning and trimming of cable ties
- Heavy duty stainless steel construction for outstanding long term performance
- Tension adjuster for the perfect tensioning of different widths of cable ties



### Cable tie gun - Heavy duty

Item Number	Length	Quantity
495004	4.7mm - 13mm	10

- Designed for automatic tensioning and trimming of cable ties
- Tension adjuster for the perfect tensioning of different widths of cable ties



### Cable tie gun

Item Number	Length	Quantity
495003	2.4mm - 4.8mm	6

## DRAW TAPES


- Special flexible spring steel for outstanding strength & reliability
- Integral braking system for non-slip cable pull through



### Electrician's draw tape cassette

Item Number	Length	Quantity
495008	50ft / 15.2m	1

- Lead spring guide for smooth feed & minimal snagging
- Special 'Perlon' tape for strength & reliability




### Electrician's draw tape

Item Number	Length	Quantity
495005	10m	3
495006	20m	3
495007	30m	3

## SWITCH KEYS

- PH2 screwdriver bit included



### Switch key - Universal 9 in 1

Item Number	Icons	Quantity
T4451-2	[Icons]	6

- Compact pen-style design offering 7 key types
- Tough glass reinforced nylon construction - strong & light weight
- Modulo size 2 screwdriver bit included



### Switch key - Universal 7 in 1

Item Number	Icons	Quantity
T4451-1	[Icons]	6

- 6mm bit driver adapter & double ended screwdriver bit included



### Switch key - Universal 8 in 1

Item Number	Icons	Quantity
495015	[Icons]	10
495002	[Icons]	10

- High quality, heavy duty construction for professional use
- Long life tips suitable for use with lead free solder
- Individually tested to 10,000V for safe live working up to 1,000V



### Soldering irons

CE, GS, ROHS 2002/95/EC, VDE0682/201, WEEE 2002/96/EC



Item Number	Power	Plug Type	Quantity
495009	soldering iron 25W	UK 3-pin plug	1
495010	soldering iron 40W	UK 3-pin plug	1
495011	soldering iron 25W	Euro 2-pin plug	1
495012	soldering iron 40W	Euro 2-pin plug	1
495013	spare tip set for 25W	-	1
495014	spare tip set for 40W	-	1


- For the fast and secure seating of data wires into terminals - suitable for a wide range of terminal block types
- One step action for automatic seating & trimming of excess wires
- Handle includes wire extractor hook & spudger



### Punch down tool

Item Number	Length	Quantity
495033	180mm 7"	3

- Precision ground, HSS tap for a clean, accurate cut & long life
- 50mm tap length for improved access
- Shatter resistant acetate handle for damage protection



### Re-threading tools

Item Number	Size	Length	Quantity
495028	M3.5	0.6	12
495029	M4	0.7	12